

# Enclosure Accessories – Miscellaneous



## Carrying Handle



| Part Number                       | Price   | Description                                                                  | Wt.[oz] |
|-----------------------------------|---------|------------------------------------------------------------------------------|---------|
| <a href="#"><u>RECH109506</u></a> | \$31.00 | Stahlin carrying handle, plastic, black. For use with fiberglass enclosures. | 2       |

## Vapor Capsule



| Part Number                   | Price   | Description                                                                                                                                                                                                                                                           | Wt.[oz] |
|-------------------------------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| <a href="#"><u>REVC21</u></a> | \$25.50 | Non-toxic vapor emitted from the capsule passivates the metal surfaces on the interior of the enclosure against atmospheric corrosion for up to one year by reducing the electro-chemical activity of the metal surfaces. Installs easily with a self-adhesive strip. | 1       |

# Enclosure Accessories – Miscellaneous



| Enclosure Pole Mount Kits                 |         |                   |                                                        |
|-------------------------------------------|---------|-------------------|--------------------------------------------------------|
| Part Number                               | Price   | For Pole Diameter | Fits                                                   |
| <b><u>PMC-7</u></b>                       | \$71.00 | 5-12 [127-304.8]  | CL707xx and CL907xx Classic series                     |
| <b><u>PMC9-11</u></b>                     | \$77.00 | 5-12 [127-304.8]  | CL1109xx and CL1311xx Classic series                   |
| <b><u>PMC-13</u></b>                      | \$83.00 | 5-12 [127-304.8]  | CL1513xx Classic series                                |
| <b><u>PMD6-8</u></b>                      | \$71.00 | 5-12 [127-304.8]  | 6in or 8in wide Diamond Shield series                  |
| <b><u>PMD10-12</u></b>                    | \$77.00 | 5-12 [127-304.8]  | 10in or 12in wide Diamond Shield series                |
| <b><u>PMD14-16</u></b>                    | \$83.00 | 5-12 [127-304.8]  | 14in or 16in wide Diamond Shield series                |
| <b><u>PMJ6-8</u></b>                      | \$72.00 | 5-12 [127-304.8]  | 6in or 8in wide J/JW/RJ/RJW series and Fatboy series   |
| <b><u>PMJ10-12</u></b>                    | \$78.00 | 5-12 [127-304.8]  | 10in or 12in wide J/JW/RJ/RJW series and Fatboy series |
| <b><u>PMJ14-16</u></b>                    | \$84.00 | 5-12 [127-304.8]  | 14in or 16in wide J/JW/RJ/RJW series and Fatboy series |
| <b><u>PMJ18-24</u></b>                    | \$97.00 | 5-12 [127-304.8]  | J2020HPL, J2420HPL, J2424HPL, and J3024HPL J series    |
| Note: Dimensions in inches [millimeters]. |         |                   |                                                        |

**PMD10-12**