# A3082007-1 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

LUTZE Silflex flexible control cable, unshielded, 7 conductors (includes ground), 20 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/A3082007-1

## Technical Specifications

| | |
|---|---|
| **Brand** | LUTZE |
| **Item** | Cable |
| **Series** | Silflex |
| **Wire/Cable Type** | Control |
| **UL Wire/Cable Type** | PLTC-ER, ITC-ER and MTW |
| **Application** | General purpose |
| **Flexibility** | Flexible |
| **Voltage Rating** | 300V (Types PLTC-ER, ITC-ER), 600V (Type MTW) |
| **Conductors** | 7 conductors (includes ground) |
| **Conductor Size** | 20 AWG |
| **Conductor Stranding** | 10-stranded |
| **Conductor Material** | Bare copper |
| **Conductor Insulation Material** | PVC/Nylon |
| **Conductor Insulation Color** | Black with white numbers and green/yellow ground |

| | |
|---|---|
| **Shielding** | Unshielded |
| **Jacket Material** | PVC |
| **Jacket Color** | Gray |
| **Nominal Overall Cable Diameter** | 0.335in |
| **Bulk Length** | Cut to length |
| **Package Type** | • 1 to 75ft = Coil<br>• 76 to 350ft = 14 x 7in Reel<br>• 351 to 500ft = 14 x 10in Reel<br>• 501 to 770ft = 16 x 10in Reel<br>• 771 to 1080ft = 18 x 10in Reel<br>• 1081 to 1410ft = 18 x 13in Reel<br>• 1411 to 3040ft = 24 x 17in Wooden Reel<br>• 3041 to 5000ft = 30 x 17in Wooden Reel<br>• 5001 to MAX = Large Wooden Reel |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E324630 |
| **UL Recognized File #** | none |
| **UL Hazardous File #** | none |
| **CSA File #** | None |
| **RoHS Status** | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| **EU REACH** | View EU REACH document |
| **Other** | RoHS Statement |