

# Accessories for OPT Series 32x12mm Photoelectric Sensors

## Right-Angle Mounting Brackets

Mounting bracket, right angle, vertical adjustment. For use with OPT series 32x12mm photoelectric sensors.

| Mounting Brackets for OPT 32x12mm Sensors |        |                                                                                                                                         |     |                            |               |
|-------------------------------------------|--------|-----------------------------------------------------------------------------------------------------------------------------------------|-----|----------------------------|---------------|
| Part Number                               | Price  | Description                                                                                                                             | Qty | Drawing Link               | Weight lb [g] |
| <a href="#"><u>OPT2033</u></a>            | \$7.00 | Wenglor mounting bracket, right-angle, vertical adjustment, nickel plated steel. For use with OPT series 32x12mm photoelectric sensors. | 1   | <a href="#"><u>PDF</u></a> | 0.04 [16]     |



[OPT2033](#)

## Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT series 32x12mm photoelectric sensors.

| Accessories for 32x12mm Sensors |         |                                                                                                                                                                                          |                     |                     |                            |               |
|---------------------------------|---------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|---------------------|----------------------------|---------------|
| Part Number                     | Price   | Description                                                                                                                                                                              | Mounting Head       | Mounting Plate      | Drawing Link               | Weight lb [g] |
| <a href="#"><u>OPT2120</u></a>  | \$11.50 | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT series 32x12mm photoelectric sensors.            | Aluminum            | 304 Stainless Steel | <a href="#"><u>PDF</u></a> | 0.14 [63.50]  |
| <a href="#"><u>OPT2121</u></a>  | \$21.00 | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with OPT series 32x12mm photoelectric sensors. | 304 Stainless Steel | 304 Stainless Steel | <a href="#"><u>PDF</u></a> | 0.27 [122.46] |



[OPT2121](#)



[OPT2120](#)

Note: 304 Stainless steel mounting rods sold separately: [OPT2109](#) (200mm length), [OPT2110](#) (300mm length), and [OPT2111](#) (500mm length).

# Mounting Rods and Brackets

## Mounting Rods

304 Stainless steel rods for mounting swivel brackets [OPT2112](#) - [OPT2127](#). Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.

| Mounting Rods for OPT2112-2127 Swivel Mounting Brackets |         |                                                                         |                     |                  |
|---------------------------------------------------------|---------|-------------------------------------------------------------------------|---------------------|------------------|
| Part Number                                             | Price   | Description                                                             | Drawing Link        | Weight lb (g)    |
| <a href="#">OPT2109</a>                                 | \$13.00 | Wenglor mounting rod, 12mm diameter, 200mm length, 304 stainless steel. | <a href="#">PDF</a> | 0.41<br>[185.97] |
| <a href="#">OPT2110</a>                                 | \$16.00 | Wenglor mounting rod, 12mm diameter, 300mm length, 304 stainless steel. | <a href="#">PDF</a> | 0.60<br>[272.16] |
| <a href="#">OPT2111</a>                                 | \$21.00 | Wenglor mounting rod, 12mm diameter, 500mm length, 304 stainless steel. | <a href="#">PDF</a> | 0.98<br>[444.52] |



## Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods [OPT2109](#), [OPT2110](#) & [OPT2111](#).

| Right-angle Mounting Brackets for 12mm Sensors |         |                                                                                                                         |                     |                |
|------------------------------------------------|---------|-------------------------------------------------------------------------------------------------------------------------|---------------------|----------------|
| Part Number                                    | Price   | Description                                                                                                             | Drawing Link        | Weight lb [g]  |
| <a href="#">OPT2108</a>                        | \$16.00 | Wenglor mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111. | <a href="#">PDF</a> | 0.07<br>[31.8] |

