



# Filter-Coalescing Filters

# SYNTESI®



Part No.  
**5U23F10D103**



Part No.  
**5U11F10D101**

Metal Work Syntesi combination units come pre-assembled with the most popular modules.

## Features

- Includes filter and coalescing filter
- Fluid - Compressed air or other inert gases
- Body size 1 or 2
- Port sizes from 1/8" NPT to 1" NPT
- Max. input pressure 217 psi (188 psi for size 2)



See [www.AutomationDirect.com](http://www.AutomationDirect.com) for a wide variety of fitting options

| Metal Work Syntesi Filter-Coalescing Filters |          |              |      |                  |                  |                     |                              |                                     |                                       |                            |                            |
|----------------------------------------------|----------|--------------|------|------------------|------------------|---------------------|------------------------------|-------------------------------------|---------------------------------------|----------------------------|----------------------------|
| Part No.                                     | Price    | Weight (lbs) | Size | Inlet(s) (NPT)   | Outlet(s) (NPT)  | Drain Bowl          | Drain Type                   | Filter                              | Coalescing Filter                     | Drawing Link               | Manufacturer Specs         |
| <a href="#"><u>5U11F10D101</u></a>           | \$83.00  | 0.85         | 1    | 1/8in female NPT | 1/8in female NPT | Clear technopolymer | Manual/ semi-automatic drain | Particulate filter element 5 micron | Coalescing filter element 0.01 micron | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>5U12F10D102</u></a>           | \$83.00  | 0.85         |      | 1/4in female NPT | 1/4in female NPT |                     |                              |                                     |                                       | <a href="#"><u>PDF</u></a> |                            |
| <a href="#"><u>5U13F10D103</u></a>           | \$83.00  | 0.85         |      | 3/8in female NPT | 3/8in female NPT |                     |                              |                                     |                                       | <a href="#"><u>PDF</u></a> |                            |
| <a href="#"><u>5U23F10D103</u></a>           | \$126.00 | 2.10         | 2    | 1/2in female NPT | 1/2in female NPT |                     |                              |                                     |                                       | <a href="#"><u>PDF</u></a> |                            |
| <a href="#"><u>5U24F10D104</u></a>           | \$126.00 | 2.05         |      | 3/4in female NPT | 3/4in female NPT |                     |                              |                                     |                                       | <a href="#"><u>PDF</u></a> |                            |
| <a href="#"><u>5U25F10D105</u></a>           | \$132.00 | 2.10         |      | 1in female NPT   | 1in female NPT   |                     |                              |                                     |                                       | <a href="#"><u>PDF</u></a> |                            |
| <a href="#"><u>5U26F10D106</u></a>           | \$132.00 | 2.05         |      | 1in female NPT   | 1in female NPT   |                     |                              |                                     |                                       | <a href="#"><u>PDF</u></a> |                            |

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).



# Accessories



| Metal Work Syntesi Accessories |                          |         |                                                                                                                                                                                               |                     |                     |              |
|--------------------------------|--------------------------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|---------------------|--------------|
| Item Photo                     | Part No.                 | Price   | Description                                                                                                                                                                                   | Drawing Link        | Manufacturer Specs  | Weight (lbs) |
|                                | <a href="#">88257E1</a>  | \$3.25  | Metal Work mounting bracket, panel, plated steel. For use with Syntesi Size 1 regulators and filter-regulators.                                                                               | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.10         |
|                                | <a href="#">88257E2</a>  | \$4.25  | Metal Work mounting bracket, panel, plated steel. For use with Syntesi Size 2 regulators and filter-regulators.                                                                               | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.10         |
|                                | <a href="#">88257E3</a>  | \$11.25 | Metal Work mounting bracket, rear, plated steel. For use with Syntesi Size 1 air prep components. Mounting hardware included.                                                                 | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.15         |
|                                | <a href="#">88257E4</a>  | \$13.00 | Metal Work mounting bracket, rear, plated steel. For use with Syntesi Size 2 air prep components. Mounting hardware included.                                                                 | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.30         |
|                                | <a href="#">9200718X</a> | \$15.50 | Metal Work DIN rail adapter, anodized aluminum. Package of 2. For use with Syntesi Size 1 and 2 air prep components. Mounting hardware included.                                              | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.20         |
|                                | <a href="#">88257E5</a>  | \$2.25  | Metal Work connector nipple, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included.                                                                  | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.05         |
|                                | <a href="#">88257E6</a>  | \$5.75  | Metal Work connector nipple, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.                                                                  | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.20         |
|                                | <a href="#">88257E7</a>  | \$3.25  | Metal Work connector nipple, 90 degree mounting, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included.                                              | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.05         |
|                                | <a href="#">88257E8</a>  | \$5.25  | Metal Work connector nipple, 90 degree mounting, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.                                              | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.20         |
|                                | <a href="#">5U11P201</a> | \$32.00 | Metal Work air distribution block, 1/8in female NPT inlet(s), (1) 1/4in female NPT and (2) 1/8in female NPT outlet(s). For use with Syntesi Size 1 air prep components.                       | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.35         |
|                                | <a href="#">5U12P202</a> | \$32.00 | Metal Work air distribution block, 1/4in female NPT inlet(s), (1) 1/8in female NPT and (2) 1/4in female NPT outlet(s). For use with Syntesi Size 1 air prep components.                       | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.35         |
|                                | <a href="#">5U13P203</a> | \$32.00 | Metal Work air distribution block, 3/8in female NPT inlet(s), (1) 1/8in female NPT, (1) 1/4in female NPT and (1) 3/8in female NPT outlet(s). For use with Syntesi Size 1 air prep components. | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.35         |
|                                | <a href="#">5U23P203</a> | \$52.00 | Metal Work air distribution block, 3/8in female NPT inlet(s), (1) 1/4in female NPT and (2) 3/8in female NPT outlet(s). For use with Syntesi Size 2 air prep components.                       | <a href="#">PDF</a> | <a href="#">PDF</a> | 1.00         |
|                                | <a href="#">5U24P204</a> | \$52.00 | Metal Work air distribution block, 1/2in female NPT inlet(s), (1) 1/4in female NPT, (1) 3/8in female NPT and (1) 1/2in female NPT outlet(s). For use with Syntesi Size 2 air prep components. | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.95         |
|                                | <a href="#">5U25P205</a> | \$59.00 | Metal Work air distribution block, 3/4in female NPT inlet(s), (1) 1/4in female NPT, (1) 3/8in female NPT and (1) 3/4in female NPT outlet(s). For use with Syntesi Size 2 air prep components. | <a href="#">PDF</a> | <a href="#">PDF</a> | 1.00         |
|                                | <a href="#">5U26P206</a> | \$59.00 | Metal Work air distribution block, 1in female NPT inlet(s), (1) 1/4in female NPT, (1) 3/8in female NPT and (1) 1in female NPT outlet(s). For use with Syntesi Size 2 air prep components.     | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.95         |
|                                | <a href="#">5U10P100</a> | \$7.25  | Metal Work air distribution block, 3/8in female NPT inlet(s), (1) 3/8in female NPT and (2) 1/8in female NPT outlet(s). For use with Syntesi Size 1 air prep components.                       | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.15         |
|                                | <a href="#">5U20P100</a> | \$19.50 | Metal Work air distribution block, 1/2in female NPT inlet(s), (1) 1/2in female NPT and (2) 3/8in female NPT outlet(s). For use with Syntesi Size 2 air prep components.                       | <a href="#">PDF</a> | <a href="#">PDF</a> | 0.25         |



# Accessories

# SYNTESI®

| Metal Work Syntesi Accessories                                                      |                                |         |                                                                                                                                            |                            |                            |              |
|-------------------------------------------------------------------------------------|--------------------------------|---------|--------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|----------------------------|--------------|
| Item Photo                                                                          | Part No.                       | Price   | Description                                                                                                                                | Drawing Link               | Manufacturer Specs         | Weight (lbs) |
|    | <a href="#"><u>88257E9</u></a> | \$2.25  | Metal Work hex bushing, G1/4 male BSPP to G1/8 female BSPP, brass. For use with Syntesi Size 2 regulators and filter-regulators.           | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.05         |
|    | <a href="#"><u>88257F1</u></a> | \$1.75  | Metal Work port adapter, 1/8in female NPT, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.05         |
|                                                                                     | <a href="#"><u>88257F2</u></a> | \$1.75  | Metal Work port adapter, 1/4in female NPT, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.05         |
|                                                                                     | <a href="#"><u>88257F3</u></a> | \$1.75  | Metal Work port adapter, 3/8in female NPT, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.05         |
|    | <a href="#"><u>88257F4</u></a> | \$5.00  | Metal Work port adapter, 3/8in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.15         |
|                                                                                     | <a href="#"><u>88257F5</u></a> | \$5.00  | Metal Work port adapter, 1/2in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|                                                                                     | <a href="#"><u>88257F6</u></a> | \$8.50  | Metal Work port adapter, 3/4in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|                                                                                     | <a href="#"><u>88257F7</u></a> | \$8.50  | Metal Work port adapter, 1in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.   | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|  | <a href="#"><u>88257F8</u></a> | \$7.50  | Metal Work pneumatic mechanical pressure gauge, 40mm diameter, 0 to 180 psi, G1/8 male BSPP process connection, center back mount.         | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.15         |
|                                                                                     | <a href="#"><u>88257F9</u></a> | \$7.50  | Metal Work pneumatic mechanical pressure gauge, 40mm diameter, 0 to 60 psi, G1/8 male BSPP process connection, center back mount.          | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.15         |
|                                                                                     | <a href="#"><u>88257G1</u></a> | \$7.50  | Metal Work pneumatic mechanical pressure gauge, 50mm diameter, 0 to 180 psi, G1/8 male BSPP process connection, center back mount.         | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.15         |
|                                                                                     | <a href="#"><u>88257G2</u></a> | \$7.50  | Metal Work pneumatic mechanical pressure gauge, 50mm diameter, 0 to 60 psi, G1/8 male BSPP process connection, center back mount.          | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.15         |
|                                                                                     | <a href="#"><u>9700110</u></a> | \$7.50  | Metal Work pneumatic mechanical pressure gauge, 40mm x 40mm, 0 to 180 psi, G1/8 male BSPP process connection, center back mount.           | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|                                                                                     | <a href="#"><u>88257G3</u></a> | \$11.75 | Metal Work pneumatic mechanical pressure gauge, 63mm diameter, 0 to 180 psi, G1/4 male BSPP process connection, center back mount.         | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.20         |
|  | <a href="#"><u>9210101</u></a> | \$26.50 | Metal Work automatic drain, for use with Syntesi Size 1 air prep components. Filter bowl included.                                         | N/A                        | <a href="#"><u>PDF</u></a> | 0.15         |
|  | <a href="#"><u>9210106</u></a> | \$32.50 | Metal Work automatic drain, for use with Syntesi Size 2 air prep components. Filter bowl included.                                         | N/A                        | <a href="#"><u>PDF</u></a> | 0.25         |



# Accessories



| Metal Work Syntesi Accessories                                                      |                         |         |                                                                                                                                                           |              |                     |              |
|-------------------------------------------------------------------------------------|-------------------------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|---------------------|--------------|
| Item Photo                                                                          | Part No.                | Price   | Description                                                                                                                                               | Drawing Link | Manufacturer Specs  | Weight (lbs) |
|    | <a href="#">9210150</a> | \$4.25  | Metal Work particulate filter element, replacement, 5 micron particles, yellow UHMWPE. For use with Syntesi Size 1 filters.                               | N/A          | <a href="#">PDF</a> | 0.05         |
|    | <a href="#">9210151</a> | \$4.25  | Metal Work particulate filter element, replacement, 20 micron particles, white UHMWPE. For use with Syntesi Size 1 filters.                               | N/A          | <a href="#">PDF</a> | 0.05         |
|    | <a href="#">9210152</a> | \$4.25  | Metal Work particulate filter element, replacement, 50 micron particles, blue HDPE. For use with Syntesi Size 1 filters.                                  | N/A          | <a href="#">PDF</a> | 0.05         |
|    | <a href="#">9210155</a> | \$5.50  | Metal Work particulate filter element, replacement, 5 micron particles, yellow UHMWPE. For use with Syntesi Size 2 filters.                               | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210156</a> | \$5.50  | Metal Work particulate filter element, replacement, 20 micron particles, white UHMWPE. For use with Syntesi Size 2 filters.                               | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210157</a> | \$5.50  | Metal Work particulate filter element, replacement, 50 micron particles, blue HDPE. For use with Syntesi Size 2 filters.                                  | N/A          | <a href="#">PDF</a> | 0.05         |
|  | <a href="#">9210160</a> | \$45.00 | Metal Work coalescing oil removal filter element, replacement, 0.01 micron particles, borosilicate glass microfiber. For use with Syntesi Size 1 filters. | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210165</a> | \$77.00 | Metal Work coalescing oil removal filter element, replacement, 0.01 micron particles, borosilicate glass microfiber. For use with Syntesi Size 2 filters. | N/A          | <a href="#">PDF</a> | 0.10         |
|  | <a href="#">9210190</a> | \$2.00  | Metal Work regulator spring, 0 to 30 psi range. For use with Syntesi Size 1 regulators.                                                                   | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210191</a> | \$2.00  | Metal Work regulator spring, 0 to 60 psi range. For use with Syntesi Size 1 regulators.                                                                   | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210192</a> | \$2.00  | Metal Work regulator spring, 0 to 120 psi range. For use with Syntesi Size 1 regulators.                                                                  | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210193</a> | \$2.00  | Metal Work regulator spring, 0 to 180 psi range. For use with Syntesi Size 1 regulators.                                                                  | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210195</a> | \$4.00  | Metal Work regulator spring, 0 to 30 psi range. For use with Syntesi Size 2 regulators.                                                                   | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210196</a> | \$4.00  | Metal Work regulator spring, 0 to 60 psi range. For use with Syntesi Size 2 regulators.                                                                   | N/A          | <a href="#">PDF</a> | 0.05         |
|                                                                                     | <a href="#">9210197</a> | \$2.75  | Metal Work regulator spring, 0 to 120 psi range. For use with Syntesi Size 2 regulators.                                                                  | N/A          | <a href="#">PDF</a> | 0.10         |
|                                                                                     | <a href="#">9210198</a> | \$3.00  | Metal Work regulator spring, 0 to 180 psi range. For use with Syntesi Size 2 regulators.                                                                  | N/A          | <a href="#">PDF</a> | 0.15         |



# Accessories



| Metal Work Syntesi Accessories                                                    |                                  |         |                                                                                                       |                            |                            |              |
|-----------------------------------------------------------------------------------|----------------------------------|---------|-------------------------------------------------------------------------------------------------------|----------------------------|----------------------------|--------------|
| Item Photo                                                                        | Part No.                         | Price   | Description                                                                                           | Drawing Link               | Manufacturer Specs         | Weight (lbs) |
|  | <a href="#"><u>88257G4</u></a>   | \$11.75 | Metal Work solenoid coil, 12 VDC, 2W, 11mm DIN style wiring plug. For use with Metal Work valves.     | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|                                                                                   | <a href="#"><u>88257G5</u></a>   | \$11.75 | Metal Work solenoid coil, 24 VDC, 2W, 11mm DIN style wiring plug. For use with Metal Work valves.     | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|                                                                                   | <a href="#"><u>88257G6</u></a>   | \$11.75 | Metal Work solenoid coil, 24 VAC, 3.5VA, 11mm DIN style wiring plug. For use with Metal Work valves.  | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|                                                                                   | <a href="#"><u>88257G7</u></a>   | \$11.75 | Metal Work solenoid coil, 110 VAC, 3.5VA, 11mm DIN style wiring plug. For use with Metal Work valves. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|                                                                                   | <a href="#"><u>88257G8</u></a>   | \$11.75 | Metal Work solenoid coil, 240 VAC, 3.5VA, 11mm DIN style wiring plug. For use with Metal Work valves. | <a href="#"><u>PDF</u></a> | <a href="#"><u>PDF</u></a> | 0.10         |
|  | <a href="#"><u>TAP-ACC21</u></a> | \$11.00 | NITRA padlock, replacement, brass. For use with TAP unit.                                             | N/A                        | N/A                        | 0.5          |



# Air Prep Components

**SYNTEsi**

Metal Work Syntesi is the result of over 30 years of air prep manufacturing. Their goal is to provide high performance and low weight in a compact, affordable package. Syntesi has many standard features unavailable with other brands.

## Features

- Lightweight yet durable bodies of technopolymer and nickel plated brass
- Additional outlet ports front and back of all modules
- Available in two body sizes
- Ports sizes from 1/8" NPT to 1" NPT

