CF211-P-02-03-02-1 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



igus continuous flexing control and signal cable, shielded, AWM, 3 twisted pairs, 24 AWG (0.25mm2), bare copper, TPE conductor insulation material, pair 1: white and brown, pair 2: green and yellow and pair 3: grey and pink, PUR jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/CF211-P-02-03-02-1

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	AWM
Applicable Standards	UL 20233
Application	General purpose
Flexibility	Continuous flexing
Voltage Rating	300V
Conductors	3 twisted pairs
Conductor Size	24 AWG (0.25mm2)
Conductor Stranding	32-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE

Conductor Insulation Color	Pair 1: white and brown, pair 2: green and yellow and pair 3: grey and pink
Shielding	Shielded
Jacket Material	PUR
Jacket Color	Gray
Nominal Overall Cable Diameter	0.276in
Bulk Length	Cut to length
Package Type	• 1 to 99ft = Coil • 100 to 510ft = 14 x 7in Reel • 511 to 730ft = 14 x 10in Reel • 731 to 1140ft = 16 x 10in Reel • 1141 to 1600ft = 18 x 10in Reel • 1601 to 1615ft = 18 x 13in Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E310776
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document