CF211-P-05-02-02-1 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



igus continuous flexing control and signal cable, shielded, AWM, 2 twisted pairs, 20 AWG (0.50mm2), bare copper, TPE conductor insulation material, pair 1: white and brown and pair 2: green and yellow, PUR jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/CF211-P-05-02-02-1

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	AWM
Applicable Standards	UL 20233
Application	General purpose
Flexibility	Continuous flexing
Voltage Rating	300V
Conductors	2 twisted pairs
Conductor Size	20 AWG (0.50mm2)
Conductor Stranding	28-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE

Conductor Insulation Color	Pair 1: white and brown and pair 2: green and yellow
Shielding	Shielded
Jacket Material	PUR
Jacket Color	Gray
Nominal Overall Cable Diameter	0.335in
Bulk Length	Cut to length
Package Type	• 1 to 75ft = Coil • 76 to 350ft = 14 x 7in Reel • 351 to 500ft = 14 x 10in Reel • 501 to 770ft = 16 x 10in Reel • 771 to 1080ft = 18 x 10in Reel • 1081 to 1410ft = 18 x 13in Reel • 1411 to 1615ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E310776
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document