CPS9Q-AP-F Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



NITRA cylinder switch, rectangular, low profile, PNP, N.O. output, 5-28 VDC operating voltage, LED indication, 0.5ft (0.15m) cable with 3-pin M8 snap-fit connector, straight cable entry, 6.5 x 3.2mm T-slot mount, for position sensing.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/CPS9Q-AP-F

Technical Specifications

Brand	NITRA
Item	Cylinder switch
Shape	Rectangular
Body Type	Low profile
Output	PNP, N.O.
Operating Voltage	5-28 VDC
Indicating Type	LED indication
Electrical Connection	0.5ft (0.15m) cable with 3-pin M8 snap-fit connector
Cable Entry	Straight
Mounting	6.5 x 3.2mm T-slot
Application	For position sensing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/CPS9Q-AP-F.pdf
See store item page for other formats.