



Filters

SYNTESI®



Part No.
5U23F203



Part No.
5U11F201

Metal Work Syntesi filters provide particulate and moisture removal in a compact package. The technopolymer bowl is more resistant to environmental stress cracking than polycarbonate.

Features

- Replaceable 20 micron filter element
- Fluid - Compressed air or other inert gases
- Body size 1 or 2
- Port sizes from 1/8" NPT to 1" NPT
- Max. input pressure 217 psi (188 psi for size 2)



See www.AutomationDirect.com for a wide variety of fitting options

Metal Work Syntesi Filters

Part No.	Price	Weight (lbs)	Size	Inlet(s) (NPT)	Outlet(s) (NPT)	Drain Bowl	Drain Type	Filter	Drawing Link	Manufacturer Specs
<u>5U11F201</u>	\$21.50	0.45	1	1/8in female NPT	1/8in female NPT	Clear technopolymer w/ guard	Manual/ semi-automatic drain	Particulate filter element 20 micron	<u>PDF</u>	<u>PDF</u>
<u>5U12F202</u>	\$21.50	0.40		1/4in female NPT	1/4in female NPT				<u>PDF</u>	
<u>5U13F203</u>	\$21.50	0.40		3/8in female NPT	3/8in female NPT				<u>PDF</u>	
<u>5U23F203</u>	\$35.00	1.05	2	1/2in female NPT	1/2in female NPT				<u>PDF</u>	
<u>5U24F204</u>	\$35.00	1.00		3/4in female NPT	3/4in female NPT				<u>PDF</u>	
<u>5U25F205</u>	\$41.50	1.05		1in female NPT	1in female NPT				<u>PDF</u>	
<u>5U26F206</u>	\$41.50	1.05							<u>PDF</u>	

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).



Accessories



Metal Work Syntesi Accessories						
Item Photo	Part No.	Price	Description	Drawing Link	Manufacturer Specs	Weight (lbs)
	88257E1	\$3.25	Metal Work mounting bracket, panel, plated steel. For use with Syntesi Size 1 regulators and filter-regulators.	PDF	PDF	0.10
	88257E2	\$4.25	Metal Work mounting bracket, panel, plated steel. For use with Syntesi Size 2 regulators and filter-regulators.	PDF	PDF	0.10
	88257E3	\$11.25	Metal Work mounting bracket, rear, plated steel. For use with Syntesi Size 1 air prep components. Mounting hardware included.	PDF	PDF	0.15
	88257E4	\$13.00	Metal Work mounting bracket, rear, plated steel. For use with Syntesi Size 2 air prep components. Mounting hardware included.	PDF	PDF	0.30
	9200718X	\$15.50	Metal Work DIN rail adapter, anodized aluminum. Package of 2. For use with Syntesi Size 1 and 2 air prep components. Mounting hardware included.	PDF	PDF	0.20
	88257E5	\$2.25	Metal Work connector nipple, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included.	PDF	PDF	0.05
	88257E6	\$5.75	Metal Work connector nipple, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.	PDF	PDF	0.20
	88257E7	\$3.25	Metal Work connector nipple, 90 degree mounting, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included.	PDF	PDF	0.05
	88257E8	\$5.25	Metal Work connector nipple, 90 degree mounting, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.	PDF	PDF	0.20
	5U11P201	\$32.00	Metal Work air distribution block, 1/8in female NPT inlet(s), (1) 1/4in female NPT and (2) 1/8in female NPT outlet(s). For use with Syntesi Size 1 air prep components.	PDF	PDF	0.35
	5U12P202	\$32.00	Metal Work air distribution block, 1/4in female NPT inlet(s), (1) 1/8in female NPT and (2) 1/4in female NPT outlet(s). For use with Syntesi Size 1 air prep components.	PDF	PDF	0.35
	5U13P203	\$32.00	Metal Work air distribution block, 3/8in female NPT inlet(s), (1) 1/8in female NPT, (1) 1/4in female NPT and (1) 3/8in female NPT outlet(s). For use with Syntesi Size 1 air prep components.	PDF	PDF	0.35
	5U23P203	\$52.00	Metal Work air distribution block, 3/8in female NPT inlet(s), (1) 1/4in female NPT and (2) 3/8in female NPT outlet(s). For use with Syntesi Size 2 air prep components.	PDF	PDF	1.00
	5U24P204	\$52.00	Metal Work air distribution block, 1/2in female NPT inlet(s), (1) 1/4in female NPT, (1) 3/8in female NPT and (1) 1/2in female NPT outlet(s). For use with Syntesi Size 2 air prep components.	PDF	PDF	0.95
	5U25P205	\$59.00	Metal Work air distribution block, 3/4in female NPT inlet(s), (1) 1/4in female NPT, (1) 3/8in female NPT and (1) 3/4in female NPT outlet(s). For use with Syntesi Size 2 air prep components.	PDF	PDF	1.00
	5U26P206	\$59.00	Metal Work air distribution block, 1in female NPT inlet(s), (1) 1/4in female NPT, (1) 3/8in female NPT and (1) 1in female NPT outlet(s). For use with Syntesi Size 2 air prep components.	PDF	PDF	0.95
	5U10P100	\$7.25	Metal Work air distribution block, 3/8in female NPT inlet(s), (1) 3/8in female NPT and (2) 1/8in female NPT outlet(s). For use with Syntesi Size 1 air prep components.	PDF	PDF	0.15
	5U20P100	\$19.50	Metal Work air distribution block, 1/2in female NPT inlet(s), (1) 1/2in female NPT and (2) 3/8in female NPT outlet(s). For use with Syntesi Size 2 air prep components.	PDF	PDF	0.25



Accessories

SYNTESI®

Metal Work Syntesi Accessories						
Item Photo	Part No.	Price	Description	Drawing Link	Manufacturer Specs	Weight (lbs)
	<u>88257E9</u>	\$2.25	Metal Work hex bushing, G1/4 male BSPP to G1/8 female BSPP, brass. For use with Syntesi Size 2 regulators and filter-regulators.	<u>PDF</u>	<u>PDF</u>	0.05
	<u>88257F1</u>	\$1.75	Metal Work port adapter, 1/8in female NPT, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included.	<u>PDF</u>	<u>PDF</u>	0.05
	<u>88257F2</u>	\$1.75	Metal Work port adapter, 1/4in female NPT, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included.	<u>PDF</u>	<u>PDF</u>	0.05
	<u>88257F3</u>	\$1.75	Metal Work port adapter, 3/8in female NPT, anodized aluminum. For use with Syntesi Size 1 air prep components. Mounting hardware included.	<u>PDF</u>	<u>PDF</u>	0.05
	<u>88257F4</u>	\$5.00	Metal Work port adapter, 3/8in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.	<u>PDF</u>	<u>PDF</u>	0.15
	<u>88257F5</u>	\$5.00	Metal Work port adapter, 1/2in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257F6</u>	\$8.50	Metal Work port adapter, 3/4in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257F7</u>	\$8.50	Metal Work port adapter, 1in female NPT, anodized aluminum. For use with Syntesi Size 2 air prep components. Mounting hardware included.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257F8</u>	\$7.50	Metal Work pneumatic mechanical pressure gauge, 40mm diameter, 0 to 180 psi, G1/8 male BSPP process connection, center back mount.	<u>PDF</u>	<u>PDF</u>	0.15
	<u>88257F9</u>	\$7.50	Metal Work pneumatic mechanical pressure gauge, 40mm diameter, 0 to 60 psi, G1/8 male BSPP process connection, center back mount.	<u>PDF</u>	<u>PDF</u>	0.15
	<u>88257G1</u>	\$7.50	Metal Work pneumatic mechanical pressure gauge, 50mm diameter, 0 to 180 psi, G1/8 male BSPP process connection, center back mount.	<u>PDF</u>	<u>PDF</u>	0.15
	<u>88257G2</u>	\$7.50	Metal Work pneumatic mechanical pressure gauge, 50mm diameter, 0 to 60 psi, G1/8 male BSPP process connection, center back mount.	<u>PDF</u>	<u>PDF</u>	0.15
	<u>9700110</u>	\$7.50	Metal Work pneumatic mechanical pressure gauge, 40mm x 40mm, 0 to 180 psi, G1/8 male BSPP process connection, center back mount.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257G3</u>	\$11.75	Metal Work pneumatic mechanical pressure gauge, 63mm diameter, 0 to 180 psi, G1/4 male BSPP process connection, center back mount.	<u>PDF</u>	<u>PDF</u>	0.20
	<u>9210101</u>	\$26.50	Metal Work automatic drain, for use with Syntesi Size 1 air prep components. Filter bowl included.	N/A	<u>PDF</u>	0.15
	<u>9210106</u>	\$32.50	Metal Work automatic drain, for use with Syntesi Size 2 air prep components. Filter bowl included.	N/A	<u>PDF</u>	0.25



Accessories



Metal Work Syntesi Accessories						
Item Photo	Part No.	Price	Description	Drawing Link	Manufacturer Specs	Weight (lbs)
	9210150	\$4.25	Metal Work particulate filter element, replacement, 5 micron particles, yellow UHMWPE. For use with Syntesi Size 1 filters.	N/A	PDF	0.05
	9210151	\$4.25	Metal Work particulate filter element, replacement, 20 micron particles, white UHMWPE. For use with Syntesi Size 1 filters.	N/A	PDF	0.05
	9210152	\$4.25	Metal Work particulate filter element, replacement, 50 micron particles, blue HDPE. For use with Syntesi Size 1 filters.	N/A	PDF	0.05
	9210155	\$5.50	Metal Work particulate filter element, replacement, 5 micron particles, yellow UHMWPE. For use with Syntesi Size 2 filters.	N/A	PDF	0.05
	9210156	\$5.50	Metal Work particulate filter element, replacement, 20 micron particles, white UHMWPE. For use with Syntesi Size 2 filters.	N/A	PDF	0.05
	9210157	\$5.50	Metal Work particulate filter element, replacement, 50 micron particles, blue HDPE. For use with Syntesi Size 2 filters.	N/A	PDF	0.05
	9210160	\$45.00	Metal Work coalescing oil removal filter element, replacement, 0.01 micron particles, borosilicate glass microfiber. For use with Syntesi Size 1 filters.	N/A	PDF	0.05
	9210165	\$77.00	Metal Work coalescing oil removal filter element, replacement, 0.01 micron particles, borosilicate glass microfiber. For use with Syntesi Size 2 filters.	N/A	PDF	0.10
	9210190	\$2.00	Metal Work regulator spring, 0 to 30 psi range. For use with Syntesi Size 1 regulators.	N/A	PDF	0.05
	9210191	\$2.00	Metal Work regulator spring, 0 to 60 psi range. For use with Syntesi Size 1 regulators.	N/A	PDF	0.05
	9210192	\$2.00	Metal Work regulator spring, 0 to 120 psi range. For use with Syntesi Size 1 regulators.	N/A	PDF	0.05
	9210193	\$2.00	Metal Work regulator spring, 0 to 180 psi range. For use with Syntesi Size 1 regulators.	N/A	PDF	0.05
	9210195	\$4.00	Metal Work regulator spring, 0 to 30 psi range. For use with Syntesi Size 2 regulators.	N/A	PDF	0.05
	9210196	\$4.00	Metal Work regulator spring, 0 to 60 psi range. For use with Syntesi Size 2 regulators.	N/A	PDF	0.05
	9210197	\$2.75	Metal Work regulator spring, 0 to 120 psi range. For use with Syntesi Size 2 regulators.	N/A	PDF	0.10
	9210198	\$3.00	Metal Work regulator spring, 0 to 180 psi range. For use with Syntesi Size 2 regulators.	N/A	PDF	0.15



Accessories



Metal Work Syntesi Accessories						
Item Photo	Part No.	Price	Description	Drawing Link	Manufacturer Specs	Weight (lbs)
	<u>88257G4</u>	\$11.75	Metal Work solenoid coil, 12 VDC, 2W, 11mm DIN style wiring plug. For use with Metal Work valves.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257G5</u>	\$11.75	Metal Work solenoid coil, 24 VDC, 2W, 11mm DIN style wiring plug. For use with Metal Work valves.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257G6</u>	\$11.75	Metal Work solenoid coil, 24 VAC, 3.5VA, 11mm DIN style wiring plug. For use with Metal Work valves.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257G7</u>	\$11.75	Metal Work solenoid coil, 110 VAC, 3.5VA, 11mm DIN style wiring plug. For use with Metal Work valves.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>88257G8</u>	\$11.75	Metal Work solenoid coil, 240 VAC, 3.5VA, 11mm DIN style wiring plug. For use with Metal Work valves.	<u>PDF</u>	<u>PDF</u>	0.10
	<u>TAP-ACC21</u>	\$11.00	NITRA padlock, replacement, brass. For use with TAP unit.	N/A	N/A	0.5



Air Prep Components

SYNTEsi

Metal Work Syntesi is the result of over 30 years of air prep manufacturing. Their goal is to provide high performance and low weight in a compact, affordable package. Syntesi has many standard features unavailable with other brands.

Features

- Lightweight yet durable bodies of technopolymer and nickel plated brass
- Additional outlet ports front and back of all modules
- Available in two body sizes
- Ports sizes from 1/8" NPT to 1" NPT

