DPM2-E-HL Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

ProSense digital panel meter, panel mount, 1/8 DIN, 14mm 4-digit red LED, AC/DC current or voltage input, 20-265 VAC/11-265 VDC operating voltage.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/DPM2-E-HL

Technical Specifications

Brand	ProSense
Item	Digital panel meter
Mounting	Panel
Mounting Hole Size	1/8 DIN
Display Type	14mm 4-digit red LED
Input	AC/DC current or voltage
Input Current Signal Range	• 0-1A AC • 0-5A AC • shunt 0-60 mVAC • shunt 0-100 mVAC • +/- 1A DC • +/- 5A DC • shunt +/- 60 mVDC • shunt +/- 100 mVDC
Input Voltage Signal Range	• 0-20 VAC • 0-200 VAC • 0-600 VAC • +/- 20 VDC • +/- 200 VDC • +/- 600 VDC
Operating Voltage	20-265 VAC/11-265 VDC
Loop Powered	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/DPM2-E-HL.pdf
See store item page for other formats.