FMM200-1002 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

ProSense liquid flow meter, magnetic-inductive, 2in female NPT process connection, 0 to 158.5 GPM, -4 to 176 F, Output: analog, Output 2: analog, 18 to 32 VDC operating voltage.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/FMM200-1002

Technical Specifications

Brand	ProSense
Item	Flow meter
Media Type	Liquid
Sensing Type	Magnetic-inductive
Process Connection	2in female NPT
Measuring Range	0 to 158.5 GPM
Measuring Range 2	-4 to 176 F
Output	Analog, 4-20 mA
Output 2	Analog, 4-20 mA
Operating Voltage	18 to 32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document