FS38-14N-P Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

HydroMode potable water push-to-connect fitting, female, straight, acetal body, acetal threads, (1) 3/8in tube to (1) 1/4in female NPT connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/FS38-14N-P

Technical Specifications

Brand	HydroMode
Item	Potable water Push-to-connect Fitting
Gender	Female
Fitting Type	Straight
Body Material	Acetal
Thread Material	Acetal
Port Connection Info	(1) 3/8in tube to (1) 1/4in female NPT
Operating Pressure	145 psi
Operating Temperature	32 to 158 deg F
Agency Approval	NSF/ANSI 61
Quantity per Pack	5

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document