# GMCBU-2D-16 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Gladiator miniature circuit breaker, 16A, 480Y / 277 VAC / 125 VDC, 2-pole, D curve, thermal magnetic, 10kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/GMCBU-2D-16

## Technical Specifications

| | |
|---|---|
| **Brand** | Gladiator |
| **Item** | Circuit breaker |
| **Circuit Breaker Type** | Miniature |
| **Circuit Type** | Feeder and branch |
| **Current-Limiting** | No |
| **Amperage Rating** | 16A |
| **Voltage Rating** | 480Y / 277 VAC / 125 VDC |
| **Number of Poles** | 2 |

| | |
|---|---|
| **Trip Curve** | D curve |
| **Trip Type** | Thermal magnetic |
| **Interrupting Rating** | 10kA @ 480Y/277 VAC |
| **UL Rating** | UL 489 listed |
| **Mounting** | 35mm DIN rail |
| **HACR Rated** | Yes |
| **Reverse Feed Capable** | Yes |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E503708 |
| **UL Recognized File #** | None |
| **UL Hazardous File #** | None |
| **CE** | View CE declarations |
| **CSA File #** | None |
| **RoHS Status** | Yes (See CE Doc) |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/GMCBU-2D-16.pdf
See store item page for other formats.