GSDA-AI-V4A Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

IronHorse GSD4A series analog input module, 1-channel, current/voltage, isolated, input current signal range(s) of 4-20 mA, input voltage signal range(s) of 0-5 VDC, 0-250 VDC.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/GSDA-AI-V4A

Technical Specifications

Brand	IronHorse
Item	Input module
I/O Module Type	Analog
Series	GSD4A
Number Of Input Channels	1
Input Signal Type(s)	Current/voltage
Analog Input Type	Sinking
Number of Isolated Commons	1
Isolated Channels	Yes
Input Current Signal Range	4-20 mA
Input Voltage Signal Range	0-5 VDC, 0-250 VDC
For Use With	IronHorse GSD4A-240-2C and GSD4A-240-6C DC drives

Agency Approvals

UL Listed File #	E198015
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/GSDA-AI-V4A.pdf
See store item page for other formats.