# GVP-3C1F-PB Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

NITRA manual valve, 3-port (3-way), 2-position, N.C., pushbutton, spring return, 90-degree ports, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), (1) vent hole exhaust(s), Cv=0.29, through panel mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/GVP-3C1F-PB

## Technical Specifications

| | |
|---|---|
| **Brand** | NITRA |
| **Item** | Valve |
| **Working Fluid** | Air |
| **Valve Type** | Manual directional control |
| **Port Quantity** | 3-port (3-way) |
| **Number Of Positions** | 2 |
| **Valve Configuration** | N.C. |
| **Operator Type** | Pushbutton |
| **Action** | Spring return |
| **Body Material** | Anodized aluminum |
| **Mounting** | Through panel |
| **Inlet Port** | 1/8in female NPT |

| | |
|---|---|
| **Outlet Port** | 1/8in female NPT |
| **Exhaust Port** | (1) vent hole |
| **Port Orientation** | 90-degree |
| **Stackable** | No |
| **Flow Coefficient** | 0.29 |
| **Maximum Operating Pressure** | 125 psi |
| **Minimum Operating Pressure** | 0 psi |
| **Form Factor** | Standard |
| **Includes** | Mounting hardware |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | None |
| **UL Recognized File #** | None |
| **UL Hazardous File #** | None |
| **CSA File #** | None |
| **RoHS Status** | No |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/GVP-3C1F-PB.pdf
See store item page for other formats.