



# StackFlow™ Inlet Port Adapters

CITO StackFlow body inlet port adapters are available in 1/2" NPT up to 1-1/2" NPT. Inlet ports can mount to the left or right-hand inlet of the modular body. The brass inlet port adapters include mounting hardware.



Part No. [EC-3401-K](#)



Part No. [EC-3121-K](#)

## Features

- Machined brass bodies
- 1/2" through 1-1/2" female NPT threaded ports
- Mounting hardware included
- Made in USA



See [www.AutomationDirect.com](http://www.AutomationDirect.com) for a wide variety of fitting options

StackFlow Inlet Port Adapters				
Part Number	Description	Drawing Link	Weight (lb)	Price
<a href="#">EC-3401-K</a>	CITO port adapter, 1/2in female NPT, brass. For use with CITO StackFlow valves body inlet. BK-9100 inlet mounting kit included.	<a href="#">PDF</a>	0.90	\$51.00
<a href="#">EC-3601-K</a>	CITO port adapter, 3/4in female NPT, brass. For use with CITO StackFlow valves body inlet. BK-9100 inlet mounting kit included.	<a href="#">PDF</a>	0.90	\$51.00
<a href="#">EC-3801-K</a>	CITO port adapter, 1in female NPT, brass. For use with CITO StackFlow valves body inlet. BK-9100 inlet mounting kit included.	<a href="#">PDF</a>	0.87	\$51.00
<a href="#">EC-3101-K</a>	CITO port adapter, 1-1/4in female NPT, brass. For use with CITO StackFlow valves body inlet. BK-9100 inlet mounting kit included.	<a href="#">PDF</a>	0.79	\$51.00
<a href="#">EC-3121-K</a>	CITO port adapter, 1-1/2in female NPT, brass. For use with CITO StackFlow valves body inlet. BK-9100 inlet mounting kit included.	<a href="#">PDF</a>	0.76	\$51.00



# Valves and Accessories

## Overview

StackFlow™ product line from CITO Products offers a robust series of modular process valves. Body sections can stack together to form a valve bank assembly with common inlets at each end and outlets discharging at the bottom of the assembly. Distribution block, manual ball valve and solenoid diaphragm valve models are available and can all be mixed in the same assembly.


## Features

- High flow capacity glass-filled nylon bodies
- Integral flow indicator available on some models
- 24 VAC/DC and 120VAC solenoids
- Cleanable inlet screens allow operation in tough environments
- Pressure and temperature gauges available
- Working fluids: water, coolant, oils
- Made in USA



See [www.AutomationDirect.com](http://www.AutomationDirect.com) for a wide variety of fitting options

## Assembly Example



For detailed assembly and configuration details, click or scan the QR code for our downloadable assembly instructions

