



Inline™ Manifolds

CITO Inline manifolds are great general purpose manifolds made from anodized aluminum. They work with air, water and many other fluids. These great looking manifolds are available in either red or blue finish.



Part No. [IM3-4-BD-8-1-8-N-R](#)



Part No. [IM3-8-BD-16-1-4-N-R](#)



Part No. [IM4-9-BD-12-1-4-N-B](#)



Part No. [IM6-10-BD-8-1-2-N-B](#)

Features

- 4, 6, or 8-stations
- Blue or red anodized aluminum
- Each station has 2 ports, one each on the 45° and 135° faces
- Each manifold includes one threaded end cap with O-ring
- Pressure rating: 3000psi @ 300°F [148.9°C]
- Works with air, inert gases, water, coolant, or oils
- Includes stainless steel mounting hardware
- Made in USA



See www.AutomationDirect.com for a wide variety of fitting options

Inline Manifold Selection

Part Number	Inlet Size	Outlet Size	Number of Stations	Body Color	Drawing Link	Weight (lb)	Price
<u>IM3-4-BD-8-1-8-N-B</u>	3/4" NPT	1/8" NPT	4	Blue	<u>PDF</u>	1.19	\$84.00
<u>IM3-4-BD-8-1-8-N-R</u>				Red	<u>PDF</u>	1.19	\$84.00
<u>IM3-6-BD-12-1-8-N-B</u>			6	Blue	<u>PDF</u>	1.58	\$108.00
<u>IM3-6-BD-12-1-8-N-R</u>				Red	<u>PDF</u>	1.58	\$108.00
<u>IM3-8-BD-16-1-8-N-B</u>			8	Blue	<u>PDF</u>	1.97	\$132.00
<u>IM3-8-BD-16-1-8-N-R</u>				Red	<u>PDF</u>	1.97	\$132.00
<u>IM3-4-BD-8-1-4-N-B</u>		1/4" NPT	4	Blue	<u>PDF</u>	1.17	\$84.00
<u>IM3-4-BD-8-1-4-N-R</u>				Red	<u>PDF</u>	1.16	\$84.00
<u>IM3-6-BD-12-1-4-N-B</u>			6	Blue	<u>PDF</u>	1.55	\$108.00
<u>IM3-6-BD-12-1-4-N-R</u>				Red	<u>PDF</u>	1.54	\$108.00
<u>IM3-8-BD-16-1-4-N-B</u>			8	Blue	<u>PDF</u>	1.92	\$132.00
<u>IM3-8-BD-16-1-4-N-R</u>				Red	<u>PDF</u>	1.91	\$132.00



Inline™ Manifolds

Inline Manifold Selection Continued							
Part Number	Inlet Size	Outlet Size	Number of Stations	Body Color	Drawing Link	Weight (lb)	Price
<u>IM4-6-BD-8-1-4-N-B</u>	1" NPT	1/4" NPT	4	Blue	<u>PDF</u>	1.92	\$105.00
<u>IM4-6-BD-8-1-4-N-R</u>				Red	<u>PDF</u>	1.93	\$105.00
<u>IM4-9-BD-12-1-4-N-B</u>			6	Blue	<u>PDF</u>	2.54	\$131.00
<u>IM4-9-BD-12-1-4-N-R</u>				Red	<u>PDF</u>	2.53	\$131.00
<u>IM4-11-BD-16-1-4-N-B</u>			8	Blue	<u>PDF</u>	3.15	\$164.00
<u>IM4-11-BD-16-1-4-N-R</u>				Red	<u>PDF</u>	3.14	\$164.00
<u>IM4-6-BD-8-3-8-N-B</u>		3/8" NPT	4	Blue	<u>PDF</u>	1.87	\$105.00
<u>IM4-6-BD-8-3-8-N-R</u>				Red	<u>PDF</u>	1.89	\$105.00
<u>IM4-9-BD-12-3-8-N-B</u>			6	Blue	<u>PDF</u>	2.50	\$131.00
<u>IM4-9-BD-12-3-8-N-R</u>				Red	<u>PDF</u>	2.48	\$131.00
<u>IM4-11-BD-16-3-8-N-B</u>			8	Blue	<u>PDF</u>	3.07	\$164.00
<u>IM4-11-BD-16-3-8-N-R</u>				Red	<u>PDF</u>	3.07	\$164.00
<u>IM6-10-BD-8-1-2-N-B</u>	1-1/2" NPT	1/2" NPT	4	Blue	<u>PDF</u>	6.36	\$162.00
<u>IM6-10-BD-8-1-2-N-R</u>				Red	<u>PDF</u>	6.37	\$162.00
<u>IM6-14-BD-12-1-2-N-B</u>			6	Blue	<u>PDF</u>	8.49	\$218.00
<u>IM6-14-BD-12-1-2-N-R</u>				Red	<u>PDF</u>	8.51	\$218.00
<u>IM6-18-BD-16-1-2-N-B</u>			8	Blue	<u>PDF</u>	10.62	\$274.00
<u>IM6-18-BD-16-1-2-N-R</u>				Red	<u>PDF</u>	10.69	\$274.00



Inline™ Manifold Accessories



Part No. [IM-3040](#)



See www.AutomationDirect.com for a wide variety of fitting options

Inline Manifold Accessories				
Part Number	Description	Drawing Link	Weight (lb)	Price
<u>IM-3030</u>	CITO manifold end cap, 3/4in male NPT, anodized aluminum. O-ring included.	<u>PDF</u>	0.10	\$12.00
<u>IM-3040</u>	CITO manifold end cap, 1in male NPT, anodized aluminum. O-ring included.	<u>PDF</u>	0.15	\$14.00
<u>IM-3060</u>	CITO manifold end cap, 1-1/2in male NPT, anodized aluminum. O-ring included.	<u>PDF</u>	0.26	\$16.00