




StackFlow™ Outlet Port Adapters

CITO StackFlow outlet port adapters are available in 1/8" NPT up to 1" NPT. Multi-port adapters available for some sizes. Mounting hardware for the brass outlet port adapters is sold separately.



Part No. [EC-2024](#)



Part No. [EC-2081](#)

Features

- Machined brass bodies
- 1/8" through 1" female NPT threaded ports
- Multi-port adapters available for 1/8" through 1/2"
- Purchase mounting hardware separately
- Bolt kit for StackShort/StackPort is BK-9750
- Bolt kit for StackFlow/StackValve is BK-9225
- Made in USA



See www.AutomationDirect.com for a wide variety of fitting options

StackFlow Body Outlet Port Adapters				
Part Number	Description	Drawing Link	Weight (lb)	Price
EC-2011	CITO port adapter, (1) 1/8in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.46	\$35.50
EC-2014	CITO port adapter, (4) 1/8in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.44	\$35.50
EC-2021	CITO port adapter, (1) 1/4in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.44	\$35.50
EC-2024	CITO port adapter, (4) 1/4in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.49	\$35.50
EC-2031	CITO port adapter, (1) 3/8in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.46	\$35.50
EC-2034	CITO port adapter, (4) 3/8in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.42	\$35.50
EC-2041	CITO port adapter, (1) 1/2in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.47	\$35.50
EC-2042	CITO port adapter, (2) 1/2in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.59	\$35.50
EC-2061	CITO port adapter, (1) 3/4in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.47	\$35.50
EC-2081	CITO port adapter, (1) 1in female NPT, brass. For use with CITO StackFlow valves body outlet.	PDF	0.43	\$35.50



Valves and Accessories

Overview

StackFlow™ product line from CITO Products offers a robust series of modular process valves. Body sections can stack together to form a valve bank assembly with common inlets at each end and outlets discharging at the bottom of the assembly. Distribution block, manual ball valve and solenoid diaphragm valve models are available and can all be mixed in the same assembly.


Features

- High flow capacity glass-filled nylon bodies
- Integral flow indicator available on some models
- 24 VAC/DC and 120VAC solenoids
- Cleanable inlet screens allow operation in tough environments
- Pressure and temperature gauges available
- Working fluids: water, coolant, oils
- Made in USA



See www.AutomationDirect.com for a wide variety of fitting options

Assembly Example



For detailed assembly and configuration details, click or scan the QR code for our downloadable assembly instructions

