



# Flow Indicators



Part No. **MF-0404-N**

CITO flow indicators use a molded turbine to indicate when fluid is flowing. They are a useful addition to many piping systems.

## Features

- 1/4" to 1" NPT threaded connections
- Smaller bodies are anodized aluminum. Larger bodies are glass-filled nylon
- Intended for use with water, coolant and oil. Use with air/gas could damage the turbine
- Made in USA



Part No. **RFH-0808**



See [www.AutomationDirect.com](http://www.AutomationDirect.com) for a wide variety of fitting options

| Flow Indicators         |                                                                                 |                           |                |            |                     |             |          |
|-------------------------|---------------------------------------------------------------------------------|---------------------------|----------------|------------|---------------------|-------------|----------|
| Part Number             | Description                                                                     | Temperature               | Pressure (psi) | Flow (gpm) | Drawing Link        | Weight (lb) | Price    |
| <b><u>MF-0404-N</u></b> | CITO MiniFlow flow indicator, 0.1-6.5 GPM, 1/4in NPT thread, anodized aluminum. | 20-210°F<br>[-6.7-98.9°C] | 1-125          | 0.1-6.5    | <a href="#">PDF</a> | 0.43        | \$124.00 |
| <b><u>MF-0606-N</u></b> | CITO MiniFlow flow indicator, 0.1-7 GPM, 3/8in NPT thread, anodized aluminum.   |                           |                | 0.1-7.0    | <a href="#">PDF</a> | 0.42        | \$124.00 |
| <b><u>RFH-0808</u></b>  | CITO RotoFlow flow indicator, 1-22 GPM, 1/2in NPT thread, glass-filled nylon.   | 20-160°F<br>[-6.7-71.1°C] | 1-100          | 1.0-22.0   | <a href="#">PDF</a> | 1.31        | \$184.00 |
| <b><u>RFH-1212</u></b>  | CITO RotoFlow flow indicator, 1-40 GPM, 3/4in NPT thread, glass-filled nylon.   |                           |                | 1.0-40.0   | <a href="#">PDF</a> | 1.29        | \$184.00 |
| <b><u>RFH-1616</u></b>  | CITO RotoFlow flow indicator, 1-60 GPM, 1in NPT thread, glass-filled nylon.     |                           |                | 1.0-60.0   | <a href="#">PDF</a> | 1.23        | \$184.00 |



# Valves and Accessories

## Overview

StackFlow™ product line from CITO Products offers a robust series of modular process valves. Body sections can stack together to form a valve bank assembly with common inlets at each end and outlets discharging at the bottom of the assembly. Distribution block, manual ball valve and solenoid diaphragm valve models are available and can all be mixed in the same assembly.


## Features

- High flow capacity glass-filled nylon bodies
- Integral flow indicator available on some models
- 24 VAC/DC and 120VAC solenoids
- Cleanable inlet screens allow operation in tough environments
- Pressure and temperature gauges available
- Working fluids: water, coolant, oils
- Made in USA



See [www.AutomationDirect.com](http://www.AutomationDirect.com) for a wide variety of fitting options

## Assembly Example



For detailed assembly and configuration details, click or scan the QR code for our downloadable assembly instructions

