# HWST242412SS Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Hammond Waterfall series enclosure, slope top, NEMA 3R/4/4X/12/13, 24 x 24 x 12in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush stainless steel.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/HWST242412SS

## Technical Specifications

| | |
|---|---|
| **Brand** | Hammond |
| **Item** | Enclosure |
| **Series** | Waterfall |
| **Subpanel** | Purchase subpanel separately |
| **Slope Top** | Yes |
| **3-Piece Assembly** | No |
| **Vented** | No |
| **NEMA Rating** | 3R/4/4X/12/13 |
| **IP Rating** | IP69K |
| **Nominal Enclosure Dimensions** | 24 x 24 x 12in (HxWxD) |
| **Enclosure Height** | 29.59in |
| **Enclosure Width** | 24.00in |
| **Enclosure Depth** | 13.21in |
| **Mounting** | Wall |
| **Integral Mounting Feet** | No |

| | |
|---|---|
| **Integral Mounting Flange** | No |
| **Dual Access** | No |
| **Knockouts** | No |
| **Bottom Gland Plate** | No |
| **Material** | 304 stainless steel |
| **Finish** | #4 brush |
| **Cover Type** | Single-door |
| **Hinge Type** | External bullet |
| **Number of Hinges Per Door** | 2 |
| **Latch Type** | 1/4-turn semi-flush stainless steel |
| **Number Of Latches** | 4 |
| **Shelf** | No |
| **Padlockable** | No |
| **Keylocking** | No |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | E65324 |
| **UL Recognized File #** | None |
| **UL Hazardous File #** | None |
| **CE** | View CE declarations |
| **CSA File #** | LR21001 |
| **RoHS Status** | Yes (See CE Doc) |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/HWST242412SS.pdf
See store item page for other formats.