KP06MD-M Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

NITRA pneumatic gripper, parallel, double acting, 6mm bore, 4mm stroke, side mount grip, anodized aluminum body, M3 x 0.5 threaded port(s).

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/KP06MD-M

Technical Specifications

Brand	NITRA
Item	Gripper
Working Fluid	Air or inert gas
Grip Type	Parallel
Action Type	Double acting
Bore Diameter	6mm
Stroke	4mm
Grip Mount Style	Side
Body Material	Anodized aluminum
Port Size	M3 x 0.5 threaded
Repeatability	+/- 0.01mm
Cycle Rate	180 cyc/min
Resulting Gripper Travel	4mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com
/static/drawings/KP06MD-M.pdf
See store item page for other formats.