

Wiring Accessories – Cutting & Stripping Tools

Wire Cutting and Stripping Tools

Self-Adjusting Cut and Strip Tools

- Widest stripping capacity of any tool of its type
- Pistol grip option (DN-WS-PG) provides stress free comfort, particularly when operating parallel to a table or workbench
- Easily interchangeable stripping cassettes are available for stripping a wide range of most modern insulation types, from PVC to PTFE; color coded by stripping blade type
- No additional tools required to change stripping blade cassettes
- Precise adjustability allows stripping of various insulation thicknesses without damage to conductors
- Easy snag-free wire removal after stripping
- Ergonomic design with soft-grip handle
- Light weight and strong; molded in high-strength plastic with twice the strength of standard nylon; tested 150k cycles
- Cutting capacity:
Stranded conductors to 8AWG (10 mm²)
Solid conductors to 16 AWG (1.5 mm²)



DN-WS Cutting & Stripping Tool


DN-WS-PG Cutting & Stripping Tool



DN-WS stripping blade replacement



DN-WSRJ



DN-WSMMC arc blade 10-5 AWG
DN-WSVBC V blade 28-12 AWG
DN-WSJ straight blade 34-8 AWG

**DN-WSxxx
Blade inserts color coded
by type**



DN-WS wire cutting

Wire Cutting and Stripping Tools

Part Number	Description	Qty	Price
DN-WS	AutomationDirect automatic cutting and stripping tool, standard grip, self-adjusting, AWG 34-8 capacity. DN-WSJ blade insert included.	1	\$77.00
DN-WS-PG	AutomationDirect automatic cutting and stripping tool, pistol grip, self-adjusting, AWG 34-8 capacity. DN-WSJ blade insert included.	1	\$121.00
DN-WSJ	DN-WS and DN-WS-PG replacement straight-blade insert; for PVC insulations; 34-8 AWG [0.02-10 mm ²]	1	\$28.50
DN-WSMMC	DN-WS and DN-WS-PG 16 mm ² blade insert; 10-5 AWG [4-16 mm ²]	1	\$60.00
DN-WSVBC	DN-WS and DN-WS-PG V-blade insert; for harder insulations such as PTFE & PVC; 28-12 AWG [0.1-4 mm ²]	1	\$38.50
DN-WSRJ	DN-WS and DN-WS-PG replacement jaw inserts	2	\$7.75
DN-CS-1	AutomationDirect heavy duty cable stripping tool, 11/64-1-9/16in capacity.	1	\$58.00
DN-CST	AutomationDirect sable stripping tool, 0.1 in (2.5mm) to 0.43 in (11mm) diameter capacity	1	\$32.50
DN-CST-BLADE	DN-CST replacement blade	1	\$10.50

Wiring Accessories – Cutting & Stripping Tools

Cable Stripping Tool **DN-CST**

Small, simple, safe, and precise tool for removing insulation from copper and fiber optic audiovisual, data transmission, instrumentation, signal, and telephone cables.

- Precise: 9-position blade height adjustment wheel for fine adjustability and repeatability
- Easy to use: Squeeze the tool together to open the stripping cavity, insert cable, rotate once, and remove tool from cable. Separately pull scrap insulation off of cable.
- Safe: Smooth, rounded, pocketable, and lightweight design; no exposed blades
- Tough: Impact resistant nylon tested to over 50k cycles
- Economical: Replacement blades available
- Cable capacity: Ø 0.1-0.43 in [2.5-11 mm]
- Insulation thickness: Up to 0.04 in [1.0 mm]



DN-CST Precision Stripping Tool
[Squeeze, insert cable, rotate, & remove]

DN-CST-BLADE Replacement Blade



Precision Stripping Tool
Easily replaceable blade

Cable Stripping Tool **DN-CS-1**

DN-CS-1 is an adjustable heavy-duty cable stripping tool for all insulation types. Unique features with interchangeable cable retention hooks giving it cable stripping capacity of up to 40 mm/1.57 inch diameter.

- Large capacity: Interchangeable hook feature means that **DN-CS-1** can replace two or more similar products in the toolbox.
- Easy to use: Positive locking positions for circular, lengthways and spiral strips.
- The blade automatically returns to its starting position at the end of a strip reducing the possibility of broken blades.
- No special tools are required to change hooks – one replaces the other. The blade height adjustor is almost friction free and is easy to rotate for fine blade height adjustment.
- Safety straps can be fixed to the eyelet at the base of **DN-CS-1** to prevent accidental dropping of the tool.
- Ergonomic: The well balanced design features rests for thumb, first and little fingers to ease raising of the cable retention hook.
- Tested to over 100,000 cycles.



Lengthways cable stripping option

DN-CS-1 Cable Stripping Tool
[circular, lengthways, and spiral strips]



Spiral cable stripping option



Circular cable stripping option