

Enclosure Accessories –

Drip Shields



Drip shields attach easily to the enclosure with stainless steel screws, gasket and sealing washers to protect door hardware from dripping water and settling dust. All mounting hardware is included. Stainless steel door clamps are furnished to replace the standard door clamps on kits for enclosures widths up to 36 in [914 mm].

DK12

SSDK12

Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1-10 days	1 - 15 days	1 - 20 days
----------	------------	------------	-----------	-------------	-------------

Color indicates shipping lead time in business days.

Drip Shield	Price	Material/Finish	For Use With	Wt.[lb]	Description
DK12	Retired	14-gauge Steel/ANSI 61 gray polyester powder	12in [305mm] NEMA 12 and NEMA 4 enclosures	0.95	Wiegmann enclosure drip shield kit. Includes 2 replacement stainless steel door clamps, integral gasket, and mounting hardware.
SSDK12	Retired	14-gauge Stainless Steel/grained finish		0.95	
DK16	Retired	14-gauge Steel/ANSI 61 gray polyester powder	16in [406mm] NEMA 12 and NEMA 4 enclosures	1.20	
SSDK16	Retired	14-gauge Stainless Steel/grained finish		0.95	
DK20	Retired	14-gauge Steel/ANSI 61 gray polyester powder	20in [508mm] NEMA 12 and NEMA 4 enclosures	1.59	Wiegmann enclosure drip shield kit. Includes 2 replacement stainless steel door clamps, integral gasket, and mounting hardware.
SSDK20	Retired	14-gauge Stainless Steel/grained finish		1.20	
DK24	Retired	14-gauge Steel/ANSI 61 gray polyester powder	24in [610mm] NEMA 12 and NEMA 4 enclosures	1.90	Wiegmann enclosure drip shield kit. Includes 3 replacement stainless steel door clamps, integral gasket, and mounting hardware.
SSDK24	Retired	14-gauge Stainless Steel/grained finish		1.59	
DK30	Retired	14-gauge Steel/ANSI 61 gray polyester powder	30in [762mm] NEMA 12 and NEMA 4 enclosures	2.40	
SSDK30	Retired	14-gauge Stainless Steel/grained finish		1.90	
DK36	Retired	14-gauge Steel/ANSI 61 gray polyester powder	36in [914mm] NEMA 12 and NEMA 4 enclosures	2.85	Wiegmann enclosure drip shield kit. Includes integral gasket and mounting hardware.
SSDK36	Retired	14-gauge Stainless Steel/grained finish		2.40	
DK42	Retired	14-gauge Steel/ANSI 61 gray polyester powder	42in [1067mm] NEMA 12 and NEMA 4 enclosures	2.98	
DK48	Retired		48in [1219mm] NEMA 12 and NEMA 4 enclosures	3.80	
DK60	Retired		60in [1524mm] NEMA 12 and NEMA 4 enclosures	4.75	
DK72	Retired		72in [1829mm] NEMA 12 and NEMA 4 enclosures	5.70	

Dimensions

