

## DIN Rail Mount EMC Shield Cable Clips SCF-EMV / MSCF-EMV Series

### Overview

The SCF-EMV / MSCF-EMV series EMC shield cable clips easily snap on to 35mm DIN rail. The spring action provides uninterrupted contact pressure with the shield enabling a conductive path to discharge EMI (electromagnetic interference).

### Features

- The spring action provides uninterrupted contact pressure with the shield
- Excellent discharge of high-frequency noise current
- Easy installation (no tools required)
- Zinc plated spring steel
- 35mm DIN rail mount

| DIN Rail Mount EMC Shield Cable Clips SCF-EMV / MSCF-EMV Series |         |                                                                                                                                                     |                 |                     |
|-----------------------------------------------------------------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|---------------------|
| Part Number                                                     | Price   | Description                                                                                                                                         | Shield Diameter | Drawing Link        |
| <a href="#">571052</a>                                          | \$25.00 | Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.06-0.12in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.  | 0.06–0.12in     | <a href="#">PDF</a> |
| <a href="#">571054</a>                                          | \$26.00 | Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.12-0.24in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.  | 0.12–0.24in     | <a href="#">PDF</a> |
| <a href="#">571056</a>                                          | \$26.00 | Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.24-0.31in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.  | 0.24–0.31in     | <a href="#">PDF</a> |
| <a href="#">571058</a>                                          | \$26.00 | Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.31-0.43in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.  | 0.31–0.43in     | <a href="#">PDF</a> |
| <a href="#">571060</a>                                          | \$30.00 | Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.43-0.63in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.  | 0.43–0.63in     | <a href="#">PDF</a> |
| <a href="#">571064</a>                                          | \$32.00 | Murrplastik SCF-EMV series EMC shield cable clip, accepts 0.67-1.18in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.  | 0.67–1.18in     | <a href="#">PDF</a> |
| <a href="#">571066</a>                                          | \$35.00 | Murrplastik SCF-EMV series EMC shield cable clip, accepts 1.18-1.46in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5.  | 1.18–1.46in     | <a href="#">PDF</a> |
| <a href="#">571070</a>                                          | \$32.00 | Murrplastik MSCF-EMV series EMC shield cable clip, accepts 0.12-0.47in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5. | 0.12–0.47in     | <a href="#">PDF</a> |
| <a href="#">571072</a>                                          | \$37.00 | Murrplastik MSCF-EMV series EMC shield cable clip, accepts 0.28-0.71in diameter cable, 35mm DIN rail mount, zinc plated spring steel. Package of 5. | 0.28–0.71in     | <a href="#">PDF</a> |



**SCF-EMV / MSCF-EMV installation  
shown with shielded cable**

## DIN Rail Mount EMC Shield Cable Clips With Strain Relief SCFZ-EMV / MSCFZ-EMV Series


### Overview

The SCFZ-EMV / MSCFZ-EMV series EMC shield cable clips with strain relief easily snap on to 35mm DIN rail. The spring action provides uninterrupted contact pressure with the shield enabling a conductive path to discharge EMI (electromagnetic interference). The strain relief tab protects the cable when using with any standard cable tie.

### Features

- The spring action provides uninterrupted contact pressure with the shield.
- Excellent discharge of high-frequency noise current
- High stability
- Easy installation (no tools required)
- Zinc plated spring steel
- 35mm DIN rail mount


| DIN Rail Mount EMC Shield Cable Clips With Strain Relief SCZF-EMV / MSCFZ-EMV Series |         |                                                                                                                                                                          |                 |                     |
|--------------------------------------------------------------------------------------|---------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|---------------------|
| Part Number                                                                          | Price   | Description                                                                                                                                                              | Shield Diameter | Drawing Link        |
| <a href="#">571074</a>                                                               | \$29.00 | Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.06-0.12in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.  | 0.06–0.12in     | <a href="#">PDF</a> |
| <a href="#">571075</a>                                                               | \$30.00 | Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.12-0.24in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.  | 0.12–0.24in     | <a href="#">PDF</a> |
| <a href="#">571076</a>                                                               | \$30.00 | Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.24-0.31in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.  | 0.24–0.31in     | <a href="#">PDF</a> |
| <a href="#">571077</a>                                                               | \$31.00 | Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.31-0.43in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.  | 0.31–0.43in     | <a href="#">PDF</a> |
| <a href="#">571078</a>                                                               | \$36.00 | Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.43-0.63in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.  | 0.43–0.63in     | <a href="#">PDF</a> |
| <a href="#">571079</a>                                                               | \$37.00 | Murrplastik SCFZ-EMV series EMC shield cable clip, accepts 0.67-0.87in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5.  | 0.67–0.87in     | <a href="#">PDF</a> |
| <a href="#">571071</a>                                                               | \$35.00 | Murrplastik MSCFZ-EMV series EMC shield cable clip, accepts 0.12-0.47in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5. | 0.12–0.47in     | <a href="#">PDF</a> |
| <a href="#">571073</a>                                                               | \$40.00 | Murrplastik MSCFZ-EMV series EMC shield cable clip, accepts 0.28-0.71in diameter cable, 35mm DIN rail mount, with strain relief, zinc plated spring steel. Package of 5. | 0.28–0.71in     | <a href="#">PDF</a> |



[571077](#)



[571071](#)



SCFZ-EMV / MSCFZ-EMV installation shown with cable tie securing cable to strain relief tab