

Enclosure Accessories – Locks and Latches

NEMA 412 Ultimate Series Tamper-Resistant Latch Kits and Keys

**N41214TTRI****N41214TVP**

Tamper-Resistant Latches			
1-point	Price	Wt.[lb]	Description
<u>N41214TTRI</u>	\$33.50	0.2	Wiegmann enclosure latch, 1/4 turn, triangular. For use on NEMA 412 Ultimate series enclosures. N41214TTRIK key required, purchased separately.
<u>N41214TVP</u>	\$59.00	0.2	Wiegmann enclosure latch, 1/4 turn, vibration proof. For use on NEMA 412 Ultimate series enclosures. N41214TVPK key required, purchased separately.

Enclosures

The latches and keys on this page are used with the following enclosure series:

- BN4_CHQT*
- BN4_CHQTSS*
- BN4_CHQTSSA*
- CTSD*
- RHC "Medium"*

*Must use cam from stock latch.

- N412_C
- N412_CLG
- N412_WC
- N412_WCLG
- N412_CST
- N412_SSC
- N412_SSAC
- N412_WSSC
- N412_CSSST
- N1C
- N1C_LP

Enclosure series example:

Enclosure part number N412121206C = N412_C series.

Enclosure Accessories – Locks and Latches

NEMA 412 Ultimate Series Lock Kits

N41214TN41214TSSN41214TWN41214TWPLN41214TTH

NEMA 412 Lock Kits						
1-point	Price	Wt. [lb]	3-point	Price	Wt. [lb]	Description
<u>N41214T</u>	\$25.50	0.2	<u>N41214T3</u>	\$56.00	2.5	Wiegmann enclosure latch, slotted, 1/4 turn. For use on NEMA 412 Ultimate series enclosures.
<u>N41214TW</u>	\$56.00	0.2	—	—	—	Wiegmann enclosure latch, wing handle, 1/4 turn. For use on NEMA 412 Ultimate series enclosures.
<u>N41214TWPL</u>	\$56.00	0.3	—	—	—	Wiegmann enclosure latch, padlocking, 1/4 turn. For use on NEMA 412 Ultimate series enclosures.
<u>N41214TTH</u>	\$99.00	0.3	—	—	—	Wiegmann enclosure latch, tee handle, 1/4 turn, black finish. For use on NEMA 412 Ultimate series enclosures.
<u>N41214TTHKL</u>	\$97.00	0.4	—	—	—	Wiegmann enclosure lock kit, 1/4 turn, key locking, black matte finish. For use on NEMA 412 Ultimate series enclosures.
<u>N41214TBKL</u> *	\$99.00	0.2	—	—	—	Wiegmann enclosure latch, black key and dust cover, 1/4 turn. For use on NEMA 412 Ultimate series enclosures.
<u>N41214TSS</u>	\$77.00	0.2	<u>N41214TSS3</u>	\$247.00	2.2	Wiegmann enclosure latch, 304 stainless steel, 1/4 turn. For use on NEMA 412 Ultimate series stainless steel enclosures. No key required

*NEMA 12 and 13 rating with dust cover only.

Enclosures

The latches and keys on this page are used with the following enclosure series:

- BN4_CHQT*
- BN4_CHQTSS*
- BN4_CHQTSSA*
- CTSD*
- RHC "Medium"*

*Must use cam from stock latch.

- N412_C
- N412_CLG
- N412_WC
- N412_WCLG
- N412_CST
- N412_SSC
- N412_SSAC
- N412_WSSC
- N412_CSSST
- N1C
- N1C_LP

Enclosure series example:

Enclosure part number N412121206C = N412_C series.

Enclosure Accessories – Locks and Latches

NEMA 1 1/4-Turn Latch



Latch	Price	Description	Wt. [lb]
<u>N1C14T</u>	\$45.00	Wiegmann enclosure latch, 1/4 turn, plated steel. For use on NEMA 1 enclosures. No key required.	0.2
<u>N1C14TKL</u>	\$56.00	Wiegmann enclosure latch, 1/4 turn key lock, plated steel and plastic construction. For use on NEMA 1 enclosures. Includes key.	0.2



N1C14TKL



N1C14T

Enclosures

The latches and keys on this page are used with the following enclosure series:

- N1C
- N1C_LP
- RHC "Medium"*
- CTSD

*Must use cam from stock latch.

Enclosure series example:

Enclosure part number N1C201606LP = N1C_LP series.

Enclosure Accessories – Locks and Latches

Latch Kits for Single Door NEMA 3R, NEMA 4, and NEMA 12 Enclosures



Latch Kits for Single Door NEMA 3R and NEMA 12 Enclosures

<i>Padlock Style</i>	<i>Price</i>	<i>Wt. [lb]</i>	<i>Description</i>
<u>WAL1C</u>	\$193.00	3.8	Wiegmann enclosure latch kit, 3-point. For use on NEMA 12 enclosures where height is 36, 42 or 48 inches.
<u>WAL1D</u>	\$192.00	4.8	Wiegmann enclosure latch kit, 3-point. For use on NEMA 12 enclosures where height is 60 or 72 inches.

Enclosures

The locks and lock kits on this page are used with the following enclosure series:
CTDD

- WA_WF

Enclosure series example:

Enclosure part number WA364812WF =
WA_WF series



WAL2A



WAL1A

Enclosure Accessories – Locks and Latches

Latch Kits for Stainless Steel Single-Door NEMA 4 and NEMA 4X Enclosures



WAL3A



WAL4A



WAL3ASS

Latch Kits for Single Door NEMA 4 and NEMA 4X Enclosures						
<i>Stainless Steel Padlock Style</i>	<i>Price</i>	<i>Wt. [lb]</i>	<i>Combo Key/ Padlock Style</i>	<i>Price</i>	<i>Wt. [lb]</i>	<i>Description</i>
<u>WAL3BSS</u>	\$156.00	3.8	—	—	—	Wiegmann enclosure latch kit, 3-point, black matte finish. For use on NEMA 4 / 4X enclosures where height is 16, 20, 24 or 30 inches.
<u>WAL3CSS</u>	\$156.00	4.5	—	—	—	Wiegmann enclosure latch kit, 3-point, black matte finish. For use on NEMA 4 / 4X enclosures where height is 36, 42 or 48 inches.
<u>WAL3DSS</u>	\$156.00	5.8	<u>WAL4D</u>	\$88.00	5.4	Wiegmann enclosure latch kit, 3-point, black matte finish. For use on NEMA 4 / 4X enclosures where height is 54 to 90 inches.

WAL Latch Kits

These latch kits are used with the following enclosure series:

- WA_FS
- WA_FSD
- WA_FSDA
- WA_FSDAD
- WA_E
- N4D_3PT
- WA_FSN43PT
- WRD_FS4
- WRD_FSD4
- N12 "Floor-Mount"
- N412_1PTC
- N412_3PTC

WAL_SS Latch Kits

These latch kits are used with the following enclosure series:

- N412_SS1PTC
- N412_SSA1PTC
- N412_SS3PTC
- N412_SSA3PTC
- SSN4_WF3PT
- SSN4_3PT
- SSN4_3PTA
- SSN4_3PTW
- SSN4D_3PT
- SSN4D_3PTA
- WA_SFSN43PT
- WA_SSFSDN43PT
- WA_FSSS
- WA_FSDSS

Enclosure series example:

Enclosure part number N4122416083PTC
= N412_3PTC series

Enclosure Accessories – Locks and Latches

Lock Kit for NEMA 4 and NEMA 12 Enclosures

This kit is designed for use as an add-on to enclosures sold without locks. Lock and key are sold separately.



Lock Kit for NEMA 4 and NEMA 12 Enclosures			
Part Number	Price	Description	Wt. [lb]
<u>WACLSN12</u>	\$33.00	Wiegmann enclosure latch with key, 1-point, plated steel. For use on NEMA 4 and NEMA 12 enclosures.	0.3



Enclosure Accessories – Locks and Latches



Replacement Clamp Assemblies

Part Number	Price	Description	Wt. [lb]
<u>WABN4JIC</u>	\$23.00	Replacement, 304 stainless steel. For use with BN4xxxxxx and BN4xxxxxxCH enclosures. Clamp and screw included.	0.1
<u>WAN12RA</u>	\$23.00	Replacement, plated steel. For use with NEMA 12 enclosures.	0.10.5
<u>WAN4XRA</u>	\$33.50	Replacement, 304 stainless steel. For use with NEMA 4X enclosures.	0.1



WABN4JIC



WAN12RA



WAN4XRA