







FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part

10 Series Casters									
Fits 									
Part Number	Part Image	Price	Description	Load Rating kg [lb]	Requires	Recommended Screw Fastener *T-Slot Attachment 2 (ADC Part Number)	Pack Quantity	Material	Drawing Link
163010		\$40.00	Leveling Caster with M12-1.75 x 35mm threaded stud (included)	250 [551]	Transport / Base Plate with M12-1.75 threaded hole	n/a	1	Die-cast aluminum/ steel/nylon/ rubber	PDF
163011		\$52.00		500 [1102]					PDF
163012		\$41.00	Leveling Caster With Mounting Plate	250 [551]	n/a	BHCS 1/4-20x7/16" (not sold by ADC)			PDF
163013		\$56.00		500 [1102]					PDF


*T-Slot Nut with 1/4 washer also required.

Caster Installation

Leveling Caster with M12-1.75 x 35mm threaded stud















Leveling Caster with mounting plate



FATH® T-Slotted Rail Accessories

Casters





- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part

15 Series Casters										
		Fits 								
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
						Core Hole Attachment 1	*T-Slot Attachment 2			
151134		\$47.00	Swivel Caster (requires Swivel Caster Adapter Plate 151136)	n/a	122 [269]	161107	n/a	1	Thermoplastic polyurethane/ nylon/steel	PDF
151135		\$40.50	Fixed Caster (requires Fixed Fixed Caster Adapter Plate 161040)			161106				PDF
151136		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134)	n/a					Steel
161040		\$3.25	3 Fixed Fixed Caster Adapter Plate	Requires Fixed Caster 151135				Die-cast zinc	PDF	
151137		\$62.00	Swivel Caster	n/a	122 [269]	n/a	161053	1	Thermoplastic polyurethane/ nylon/steel	PDF
151138		\$49.00	Fixed Caster				PDF			
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a			
163011		\$52.00			500 [1102]	PDF				
163012		\$41.00			n/a	250 [551]	151040	PDF		
163013		\$56.00				500 [1102]		PDF		

*T-Slot Nut also required

FATH® T-Slotted Rail Accessories







Casters - Continued

Caster Installation	
Swivel Caster	
Fixed Caster	
Leveling Caster with bolt hole thread	
Leveling Caster with mounting plate	

FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part

30 Series Casters										
		Fits 								
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
						Core Hole Attachment 1	*T-Slot Attachment 2			
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]	n/a	n/a	1	Die-cast aluminum/steel/nylon/rubber	PDF
163011		\$52.00			500 [1102]					PDF
163012		\$41.00	Leveling Caster	n/a	250 [551]	n/a	161059	1	Die-cast aluminum/steel/nylon/rubber	PDF
163013		\$56.00			500 [1102]					PDF


*T-Slot Nut also required.

Caster Installation

Leveling Caster with bolt hole thread















Leveling Caster with mounting plate



FATH® T-Slotted Rail Accessories

Casters





- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part

40 Series Casters										
		Fits 								
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
						Core Hole Attachment 1	*T-Slot Attachment 2			
151134		\$47.00	Swivel Caster (requires Swivel Caster Adapter Plate 151136)	n/a	122 [269]	161107	n/a	1	Thermoplastic polyurethane/ nylon/steel	PDF
151135		\$40.50	Fixed Caster (requires Fixed Fixed Caster Adapter Plate 161040)			161106				PDF
151136		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134)	n/a	PDF				
161040		\$3.25	3 Fixed Fixed Caster Adapter Plate	Requires Fixed Caster 151135	n/a	PDF				
151137		\$62.00	Swivel Caster	n/a	122 [269]	n/a	161053	1	Thermoplastic polyurethane/ nylon/steel	PDF
151138		\$49.00	Fixed Caster							PDF
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a		161060	
163011		\$52.00			500 [1102]	PDF				
163012		\$41.00			250 [551]	PDF				
163013		\$56.00			500 [1102]	PDF				

*T-Slot Nut also required

FATH® T-Slotted Rail Accessories













Casters - Continued

Caster Installation	
Swivel Caster	
Fixed Caster	
Leveling Caster with bolt hole thread	
Leveling Caster with mounting plate	

FATH® T-Slotted Rail Accessories

Casters




- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part

45 Series Casters										
		Fits 		 <p>45 Series (mm) 45x45 45x90 90x90</p>						
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
						Core Hole Attachment 1	*T-Slot Attachment 2			
151134		\$47.00	Swivel Caster	Requires Swivel Caster Adapter Plate 151261	122 [269]	161111		1	Thermoplastic polyurethane/nylon/steel	PDF
151135		\$40.50	Fixed Caster	Requires Fixed Caster Adapter Plate 161041						161110
151261		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134	n/a			1	Steel	PDF
161041		\$3.25	3 Fixed Caster Adapter Plate	Requires Fixed Caster 151135					Die-cast zinc	PDF
151137		\$62.00	Swivel Caster	n/a	122 [269]		161066	1	Thermoplastic polyurethane/nylon/steel	PDF
151138		\$49.00	Fixed Caster							PDF
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a	1	Die-cast aluminum/steel/nylon/rubber	PDF
163011		\$52.00			500 [1102]					PDF
163012		\$41.00		n/a	250 [551]	161061	PDF			
163013		\$56.00			500 [1102]		PDF			

*T-Slot Nut also required

FATH[®] T-Slotted Rail Accessories

Casters - Continued

Caster Installation	
Swivel Caster	
Fixed Caster	
Leveling Caster with bolt hole thread	
Leveling Caster with mounting plate	