

FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part

15 Series Casters												
Fits		Slot Size 	15 Series (inch)  1.5x1.5 1.5x3 3x3									
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link		
						Core Hole Attachment 1	*T-Slot Attachment 2					
151134		\$47.00	Swivel Caster (requires Swivel Caster Adapter Plate 151136)	n/a	122 [269]	161107	n/a	1	Thermoplastic polyurethane/ nylon/steel	PDF		
151135		\$40.50	Fixed Caster (requires Fixed Fixed Caster Adapter Plate 161040)			161106				PDF		
151136		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134)	n/a	n/a			Steel	PDF		
161040		\$3.25	3 Fixed Fixed Caster Adapter Plate	Requires Fixed Caster 151135			Die-cast zinc		PDF			
151137		\$62.00	Swivel Caster	n/a	122 [269]	n/a	161053		Thermoplastic polyurethane/ nylon/steel	PDF		
151138		\$49.00	Fixed Caster				PDF					
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a		Die-cast aluminum/ steel/nylon/ rubber	PDF		
163011		\$52.00			500 [1102]					PDF		
163012		\$41.00		n/a	250 [551]		151040			PDF		
163013		\$56.00			500 [1102]					PDF		
*T-Slot Nut also required												

*T-Slot Nut also required

FATH® T-Slotted Rail Accessories

Casters - Continued



FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part

30 Series Casters											
		Fits		Slot Size 8		30 Series (mm) 30x30 30x60 60x60					
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link	
						Core Hole Attachment 1	*T-Slot Attachment 2				
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]	n/a	n/a	1	Die-cast aluminum/ steel/nylon/ rubber	PDF	
163011		\$52.00			500 [1102]					PDF	
163012		\$41.00		n/a	250 [551]		161059			PDF	
163013		\$56.00			500 [1102]					PDF	
*T-Slot Nut also required.											


*T-Slot Nut also required.

Caster Installation

Leveling Caster with bolt hole thread



Leveling Caster with mounting plate



FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part

40 Series Casters										
Fits		Slot Size 8		40 Series (mm) 40x40 40x80 80x80						
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
						Core Hole Attachment 1	*T-Slot Attachment 2			
151134		\$47.00	Swivel Caster (requires Swivel Caster Adapter Plate 151136)	n/a	122 [269]	161107	n/a	1	Thermoplastic polyurethane/ nylon/steel	PDF
151135		\$40.50	Fixed Caster (requires Fixed Fixed Caster Adapter Plate 161040)			161106				PDF
151136		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134)	n/a	n/a			Steel	PDF
161040		\$3.25	3 Fixed Fixed Caster Adapter Plate	Requires Fixed Caster 151135					Die-cast zinc	PDF
151137		\$62.00	Swivel Caster	n/a	122 [269]	n/a	161053		Thermoplastic polyurethane/ nylon/steel	PDF
151138		\$49.00	Fixed Caster							PDF
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a	Die-cast aluminum/ steel/nylon/ rubber	PDF	
163011		\$52.00			500 [1102]				PDF	
163012		\$41.00		n/a	250 [551]		161060		PDF	
163013		\$56.00			500 [1102]				PDF	
*T-Slot Nut also required										

*T-Slot Nut also required

FATH® T-Slotted Rail Accessories

Casters - Continued



FATH® T-Slotted Rail Accessories

Casters

- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part

45 Series Casters										
		Slot Size 10		45 Series (mm)						
		Fits								

FATH® T-Slotted Rail Accessories

Casters - Continued

