P2-04DA Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Productivity2000 analog output module, 4-channel, current/voltage, 16-bit, output current signal range(s) of 4-20 mA, output voltage signal range(s) of +/- 10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/P2-04DA

Technical Specifications

Brand	Productivity2000
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	4
Output Signal Type	Current/voltage
Analog Output Type	Sinking/sourcing
Isolated Channels	No
Number of Non-Isolated Output Commons	2
Output Resolution	16-bit
Output Current Signal Range	4-20 mA
Output Voltage Signal Range	+/- 10 VDC
Display Type	4 x 10 character OLED display
External Power Requirement	24 VDC
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v2.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document