PN12C Cut Sheet



PBC Simplicity series single pillow block, plain bearing, 1.88in overall length, PTFE, 3/4in inside diameter, aluminum housing, 0.0015in running clearance. For use with 3/4in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/PN12C

Technical Specifications

Brand	PBC
Item	Single pillow block
Series	Simplicity
Block Type	Open type
Overall Length	1.88in
Bearing Type	Plain bearing
Bearing Material	PTFE
Housing Fit	Self-aligning
Bearing Inside Diameter	3/4in
Housing Material	Aluminum
Running Clearance	0.0015in
For Use With	3/4in diameter PBC shafts

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/PN12C.pdf
See store item page for other formats.