PSD25-0P-0145H Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

ProSense electronic pressure switch, 7.5 to 145 psi set point, 316 stainless steel sensing element, PNP, N.O./N.C. complementary, 1/4in male NPT process connection, 9.6-32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/PSD25-0P-0145H

Technical Specifications

Brand	ProSense
Item	Electronic pressure switch
Media Type	Air and gases
Setpoint Range	7.5 to 145 psi
Wetted Parts	Stainless steel
Sensing Element Material	316 stainless steel
Switching Output	PNP, N.O./N.C. complementary
Process Connection	1/4in male NPT
Operating Voltage	9.6-32 VDC
IP Rating	IP67
Indicating Type	LED indication
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/PSD25-0P-0145H.pdf
See store item page for other formats.