PX-418 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Protos X analog output terminal, 8-channel, voltage, 12-bit, output voltage signal range(s) of +/- 10 VDC.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/PX-418

Technical Specifications

Brand	Protos X
Item	Output terminal
I/O Module Type	Analog
Number Of Output Channels	8
Output Signal Type	Voltage
Isolated Channels	No
Output Resolution	12-bit
Output Voltage Signal Range	+/- 10 VDC

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/PX-418.pdf
See store item page for other formats.