Q4170-1 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Quabbin control and signal cable, shielded, 3 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/Q4170-1

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2093
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	3 conductors
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, red and clear

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.235in
Bulk Length	Cut to length
Package Type	• 1 to 99ft = Coil • 100 to 709ft = 14 x 7in Reel • 710 to 1014ft = 14 x 10in Reel • 1015 to 1569ft = 16 x 10in Reel • 1570 to 2209ft = 18 x 10in Reel • 2210 to 2872ft = 18 x 13in Reel • 2873 to 6169ft = 24 x 17in Wooden Reel • 6170 to 10143ft = 30 x 17in Wooden Reel • 10144 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976,E118830
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement