Q7315-1 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Quabbin control and signal cable, shielded, 2 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/Q7315-1

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 20093
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black and red

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.135in
Bulk Length	Cut to length
Package Type	• 1 to 99ft = Coil • 100 to 2150ft = 14 x 7in Reel • 2151 to 3000ft = 14 x 10in Reel • 3001 to 4700ft = 16 x 10in Reel • 4701 to 6600ft = 18 x 10in Reel • 6601 to 8700ft = 18 x 13in Reel • 8701 to 18000ft = 24 x 17in Wooden Reel • 18001 to 30000ft = 30 x 17in Wooden Reel • 30001 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976,E118830
CE	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement