RIA.2.233 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

SapiSelco releasable cable tie, 11.02in length, 0.3in width, 79.37lb tensile strength, 2.99in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/RIA.2.233

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Releasable
Length	11.02in
Width	0.3in
Tensile Strength	79.37lb
Maximum Bundle Diameter	2.99in
Color	Natural
Material	Nylon
Temperature Rating	+5 to +167 deg F
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document