RTDW-22-1U-P-1 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

TE Wire & Cable RTD extension wire, unshielded, 3 conductors, 22 AWG, tinned copper, PVC conductor insulation material, (1) white and (2) red, PVC jacket, white, cut to length.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/RTDW-22-1U-P-1

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	RTD
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	3 conductors
Conductor Size	22 AWG
Conductor Stranding	7/30-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	(1) white and (2) red

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	White
Nominal Overall Cable Diameter	0.16in
Bulk Length	Cut to length
Package Type	• 1 to 250ft = Coil • 251 to 1446ft = 14 x 7in Reel • 1447 to 2066ft = 14 x 10in Reel • 2067 to 3196ft = 16 x 10in Reel • 3197 to 4501ft = 18 x 10in Reel • 4502 to 5852ft = 18 x 13in Reel • 5853 to 12570ft = 24 x 17in Wooden Reel • 12571 to 20667ft = 30 x 17in Wooden Reel • 20668 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement