SEL.3.426 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

SapiSelco general purpose cable tie, 14.17in length, 0.18in width, 61.73lb tensile strength, 3.98in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/SEL.3.426

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Length	14.17in
Width	0.18in
Tensile Strength	61.73lb
Maximum Bundle Diameter	3.98in
Color	Black
Material	Nylon
Temperature Rating	-40 to +185 deg F
Quantity per Pack	100

Agency Approvals

UL Listed File #	E160935
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document