

# Enclosure Accessories



## Barrier Kits for HN4WM NEMA 4 Wall-Mount Enclosures



### Application

- Barrier kits are designed to provide 2 vertical sections within double-door, NEMA 4 enclosures
- For use with HN4WM wall-mount enclosures
- Can provide separation between power and control sections within one enclosure
- Does NOT provide complete physical separation as there is space above and below the barrier to run wiring
- Depth mounted - bolted to the subpanel at rear and the center post at front
- Subpanels are steel and painted RAL9003 white
- Mounting hardware included

Barrier Kits for HN4WM NEMA 4 Wall-Mount Enclosures			
Part Number	Price	Enclosure Size HxD	Drawing Link
<a href="#">BKWM2408</a>	\$155.00	24.00 x 8.00 [610 x 203]	<a href="#">PDF</a>
<a href="#">BKWM3010</a>	\$171.00	30.00 x 10.00 [762 x 254]	<a href="#">PDF</a>
<a href="#">BKWM3612</a>	\$193.00	36.00 x 12.00 [914 x 305]	<a href="#">PDF</a>
<a href="#">BKWM4212</a>	\$201.00	42.00 x 12.00 [1067 x 305]	<a href="#">PDF</a>
<a href="#">BKWM4812</a>	\$229.00	48.00 x 12.00 [1219 x 305]	<a href="#">PDF</a>
Note: Dimensions in inches [millimeters].			

## Barrier Kits for NEMA 4 Floor-Mount Enclosures



### Application

- Barrier kits are designed to provide 2 vertical sections within double-door, NEMA 4 enclosures.
- For use with HN4FM Series and 1422N4 enclosures
- Can provide separation between power and control sections within one cabinet
- Does NOT provide complete physical separation as there is space above and below the barrier to run wiring
- Depth mounted - bolted to the subpanel at rear and the center post at front
- Certain sizes are depth adjustable
- Subpanels are steel and painted RAL9003 white
- Mounting hardware included

Barrier Kits for NEMA 4 Floor-Mount Enclosures				
Part Number	Price	Fits Enclosure Height	Fits Enclosure Depth	Drawing Link
<a href="#">BKFM6012</a>	\$255.00	60 [1524]	10 [254] or 12 [305]	<a href="#">PDF</a>
<a href="#">BKFM6018</a>	\$278.00	60 [1524]	18 [457]	<a href="#">PDF</a>
<a href="#">BKFM7218</a>	\$286.00	72 [1829]	12 [305] or 18 [457]	<a href="#">PDF</a>
<a href="#">BKFM7224</a>	\$312.00	72 [1829]	24 [610]	<a href="#">PDF</a>
Note: Dimensions in inches [millimeters].				