

Enclosure Accessories



Drip Shield Kit



Application

- Easily installed on NEMA 12, 4, and 4X wall-mount enclosures using stainless steel bolts and sealing washers (included).
- Designed not to interfere with door clamps.
- Protects door from dripping water and settling dust.
- Constructed in 14-gauge mild steel (painted) or 316 stainless steel.
- Maintains enclosure rating.

Drip Shield Kit - DK Series							
ANSI 61 Gray	Price	RAL7035 Lt Gray	Price	Stainless Steel	Price	Fits Enclosure Width (in.)	Drawing Link
DK12GY	\$62.00	DK12LG	\$62.00	DK12S16	\$136.00	12.0 [305]	PDF
DK16GY	\$68.00	DK16LG	\$68.00	DK16S16	\$147.00	16.0 [406]	PDF
DK20GY	\$74.00	DK20LG	\$74.00	DK20S16	\$160.00	20.0 [508]	PDF
DK24GY	\$81.00	DK24LG	\$81.00	DK24S16	\$173.00	24.0 [610]	PDF
DK30GY	\$91.00	DK30LG	\$91.00	DK30S16	\$193.00	30.0 [762]	PDF
DK36GY	\$99.00	DK36LG	\$99.00	DK36S16	\$211.00	36.0 [914]	PDF
DK42GY	\$110.00	DK42LG	\$110.00	DK42S16	\$224.00	42.0 [1067]	PDF
DK48GY	\$118.00	DK48LG	\$118.00	DK48S16	\$236.00	48.0 [1219]	PDF
DK60GY	\$136.00	DK60LG	\$136.00	DK60S16	\$276.00	60.0 [1524]	PDF
DK72GY	\$153.00	—	—	DK72S16	\$307.00	72.0 [1829]	PDF

Note: Dimensions in inches [millimeters].

Pedestal Columns and Bases for Operator Consoles



Pedestal Column



Pedestal Base

Application

- Used for floor-mounting many types of enclosures, consolets or pushbutton boxes.
- Provides wiring feature through the column.

Pedestal Column

- Columns are formed from 14-gauge steel with 10-gauge flanges.
- Column access opening with gasketed cover.
- Columns include flange gaskets and a box connector.

Pedestal Base

- Bases are formed from 10-gauge steel with additional reinforcing.

Pedestal Columns and Bases for Operator Consoles			
Part Number	Price	Description	Drawing Link
1495C35	\$314.00	Straight pedestal column, carbon steel, 35.00 x 4.00 x 4.00in, ANSI 61 gray, powder coat finish. For use with operator consolets. Flange gaskets, box connector and mounting hardware included.	PDF
1495D35	\$470.00	Straight pedestal column, carbon steel, 35.00 x 6.00 x 6.00in, ANSI 61 gray, powder coat finish. For use with operator consolets. Flange gaskets, box connector and mounting hardware included.	PDF
1495XK	\$195.00	Pedestal base, carbon steel, 18.00 x 18.00in, ANSI 61 gray, powder coat finish. For use with pedestal columns. Leveling screws included.	PDF
1495XN	\$433.00	Pedestal base, carbon steel, 24.00 x 24.00in, ANSI 61 gray, powder coat finish. For use with pedestal columns. Leveling screws included.	PDF

Note: Dimensions in inches [millimeters].