

# Enclosure Accessories

## Hole Seals and Plugs



Carbon Steel



Stainless Steel

### Features

- Designed to seal unused pushbutton holes, conduit openings and knockout holes against dust, oil, and water.
- Available in carbon with ANSI gray finish and 304 stainless steel with #4 brushed finish.
- Oil-resistant gasket.
- Secured with an 10-24 x 0.55in [14 mm] threaded stud and plated wing nut.

Hole Seals						
Carbon Steel	Price	Stainless Steel	Price	Max Hole Diameter	Overall Seal Diameter	Drawing Link
<a href="#">HP22</a>	\$6.50	<a href="#">HP22SS</a>	\$16.50	0.88 [22]	1.22 [31]	<a href="#">PDF</a>
<a href="#">HP50</a>	\$6.50	<a href="#">HP50SS</a>	\$16.50	0.88 [22]	1.38 [35]	<a href="#">PDF</a>
<a href="#">HP75</a>	\$8.25	<a href="#">HP75SS</a>	\$21.00	1.06 [27]	1.56 [40]	<a href="#">PDF</a>
<a href="#">HPB</a>	\$8.75	<a href="#">HPBSS</a>	\$23.50	1.25 [32]	1.75 [44]	<a href="#">PDF</a>
<a href="#">HP100</a>	\$11.25	<a href="#">HP100SS</a>	\$28.50	1.38 [35]	1.88 [48]	<a href="#">PDF</a>
<a href="#">HP125</a>	\$12.50	<a href="#">HP125SS</a>	\$32.50	1.69 [43]	2.19 [56]	<a href="#">PDF</a>
<a href="#">HP150</a>	\$14.25	<a href="#">HP150SS</a>	\$37.00	2.00 [51]	2.50 [64]	<a href="#">PDF</a>
<a href="#">HP200</a>	\$15.75	<a href="#">HP200SS</a>	\$41.00	2.50 [64]	3.00 [76]	<a href="#">PDF</a>
<a href="#">HP250</a>	\$20.00	—	—	3.00 [76]	3.50 [89]	<a href="#">PDF</a>
<a href="#">HP350</a>	\$34.50	—	—	4.12 [92]	4.12 [105]	<a href="#">PDF</a>
<a href="#">HP300</a>	\$26.50	—	—	3.62 [105]	4.62 [117]	<a href="#">PDF</a>
<a href="#">HP400</a>	\$44.00	—	—	4.62 [117]	5.12 [130]	<a href="#">PDF</a>
Note: Dimensions in inches [millimeters].						