

Enclosure Accessories

Locks and Latches



Door Clamps



1481HC18

Features

- Replacement hardware for use on all 1418 and 1447 series Hammond enclosures.
- Formed heavy gauge stainless steel clamp with stainless steel hardware.
- Sold in sets of two.



1481C14

Features

- Replacement hardware for use on 1414, HJ, 1485, 1486, and 1487 series Hammond enclosures.
- Formed heavy gauge stainless steel.
- Sold in sets of two.

Door Clamp for 1418 and 1447 Hammond Enclosures

Part Number	Price	Fits Enclosure Series	Material	Drawing Link
1481HC18	\$44.50	1418 and 1447	316 stainless steel	PDF
1481C14	\$24.00	HJ, 1414, 1485, 1486 and 1487	304 stainless steel	PDF

Quick Release Clamp



Features

- Installs easily on standard clamp bracket allowing for quick access.
- Compatible with 1414 and HJ Series junction boxes. Also 1485 Series wireway and 1486 trough.
- Available in plated or stainless steel.
- Sold Individually.

Junction Box Quick Release Clamp

Part Number	Price	Material	Drawing Link
14QR	\$13.00	zinc plated steel	PDF
14QRSS	\$27.50	304 stainless steel	PDF
14QRS16	\$33.50	316 stainless steel	PDF

Wall-Mount Quick Release Clamp



Features

- Provides fast access to conventional screw clamp type enclosures.
- Installs on clamp bracket in place of screw on 1418, 1418N4, 1447N4, and 1422N4 Series enclosures.
- Entire assembly is 304 stainless steel.
- Set of two.

Wall-Mount Quick Release Clamp

Part Number	Price	Material	Drawing Link
1418QR	\$31.50	304 stainless steel	PDF

Enclosure Accessories

Locks and Latches



Padlock Kit



Features

- Field installed kit requires drilling of only 4 holes.
- Compatible with 1414 and HJ enclosures.
- Only available in 316 stainless steel.
- Includes mounting hardware.
- Sold Individually.
- Installation instructions provided.

Padlock Kit		
Part Number	Price	Drawing Link
14PLKS16	\$23.50	PDF

NEMA 1 Lock Kits



Features

- Keylocking, 1-point, 1/4-turn, flush-mount latch.
- Installs in place of the existing slotted latch, or in cutout hole provided.
- Reversible cam position for other applications.
- Maintains NEMA 1 rating.

NEMA 1 Lock Kit				
Part Number	Price	Fits Enclosures	Material	Drawing Link
1427LKN1	\$36.00	1420 and N1A	plated steel	PDF
N1JLK	\$9.50	N1J, CHKO, N1WS, N1WF, and SWB	polyamide	PDF

Padlock Adaptor

EJ Series



Features

- For use with Eclipse Junior (EJ) Series enclosures.
- Padlock adaptor fits directly over the slotted quarter turn preventing access.
- 2mm thick 14-gauge stainless steel.
- Stainless steel mounting hardware provided.
- Once installed, the bolts cannot be removed without the door open.
- Easy installed in the field.
- Padlock not included.
- Maintains UL/CSA Type 4, and 4X rating.

Padlock Adaptor Eclipse and Series 2000		
Part Number	Price	Drawing Link
EJPA	\$23.50	PDF

Padlock Adaptor

Eclipse and Series 2000



Features

- For use with EN4SD /S2000 Series Enclosures.
- Padlock adaptor fits directly over the slotted quarter turn preventing access.
- 14-gauge 304 stainless steel.
- Stainless steel mounting hardware provided.
- Once installed, the bolts cannot be removed without the door open.
- Easy installed in the field.
- Padlock not included.
- Maintains UL/CSA Type 4 and 4X rating.

Padlock Adaptor EJ Series		
Part Number	Price	Drawing Link
EPA	\$25.00	PDF

Enclosure Accessories

Locks and Latches



1/4-Turn Inserts and Keys

Features

- For Eclipse Series enclosures.
- Field installable inserts replace standard 1/4-turn slot.
- Available in square and triangle formats, as well as slotted.
- Maintains NEMA, UL and CSA 12, 4, and 4X ratings.
- Non-slot inserts provide extra security since standard screw drivers cannot open.
- Keys constructed from die-cast zinc.
- Keys sold separately from inserts.



1/4-Turn Inserts and Keys								
Latch Insert	Price	Type	Material	Finish	Drawing Link	Key	Price	Finish
2SQI7	\$18.00	square key	die-cast zinc	black matte	PDF	2SQK7	\$16.75	black matte
2TRI7	\$18.00	triangular key	die-cast zinc	black matte	PDF	2TRK7	\$16.75	natural
2SLI	\$18.00	slotted	die-cast zinc	black matte	PDF	—	—	—
2DBI3	\$18.00	3mm double-bit	die-cast zinc	black matte	PDF	PMKEY	\$16.50	black matte
2DBI3SS	\$45.00	3mm double-bit	stainless steel	natural	PDF	PMKEY	\$16.50	natural



1/4-Turn Latch Assemblies

Features

- Field installable.
- Interchangeable with standard 1/4-turn latches on Eclipse or Eclipse Jr series.
- Maintains NEMA, UL, and CSA ratings of enclosures.
- Keylocking latch assemblies include two keys.



1/4-Turn Latch Assemblies							
Part Number	Price	Style	Security	Material	Finish	For Use With	Drawing Link
EQTRL	\$24.50	1/4-turn semi-flush	keylocking	die-cast zinc	chrome	Eclipse series swing-out panels	PDF
2QTR	\$18.25	1/4-turn semi-flush	slotted	die-cast zinc	black matte	Eclipse series	PDF
2SSQTR	\$68.00	1/4-turn semi-flush	slotted	316 stainless steel	—	Eclipse series	PDF
2WKL	\$99.00	1/4-turn wing handle	keylocking	die-cast zinc	black matte	Eclipse series	PDF
2QPL	\$84.00	1/4-turn knob	padlocking	die-cast zinc	black matte	Eclipse series	PDF
EJQTR	\$15.00	1/4-turn semi-flush	slotted	die-cast zinc	black matte	Eclipse Junior series	PDF
EJSSQTR	\$47.00	1/4-turn semi-flush	slotted	316 stainless steel	—	Eclipse Junior series	PDF
EJWKL	\$46.00	1/4-turn wing handle	keylocking	die-cast zinc	black matte	Eclipse Junior series	PDF
EJWKNL	\$46.00	1/4-turn wing handle	—	die-cast zinc	black matte	Eclipse Junior series	PDF

Enclosure Accessories

Locks and Latches



Waterfall Accessory Latch and Key			
Part Number	Price	Description	Drawing Link
EFGK	\$16.75	Hollow female round, 316L stainless steel. Package of 1. For use with EQTFG latches.	PDF
EQTFG	\$68.00	Replacement, easy-to-clean round, 1/4-turn sanitary, 1-point, 316L stainless steel. Package of 1. For use with Waterfall series enclosures. Requires EFGK key.	PDF
Note: Dimensions in inches [millimeters].			

Enclosure Accessories

Locks and Latches



1/4-Turn Latch Handles



Features

- Durable zinc diecast or stainless steel.
- Removable handle stop for clockwise / counter-clockwise operation.
- Textured powder coat Black finish on zinc cast handle.
- Maintains NEMA rating of enclosure.
- Padlock "trigger" design for security requirements.
- Optional key lock or defeater available. Key lock versions include two keys.

1/4-Turn Latch Handles							
Part Number	Price	Security Type	Latch Points	Material	Finish	For Use With These Hammond Enclosures Only	Drawing Link
MHK1	\$127.00	padlocking	1	die-cast zinc	black matte	single-door NEMA 4 and NEMA 12	PDF
MHKD1	\$133.00	padlocking with defeater					PDF
MHKL1	\$144.00	combination keylocking/ padlocking					PDF
MHK2	\$217.00	padlocking	3	die-cast zinc	black matte	less than 60in (H) NEMA 4 and NEMA 12	PDF
MHKD2	\$228.00	padlocking with defeater					PDF
MHKL2	\$246.00	combination keylocking/ padlocking					PDF
MHK3	\$221.00	padlocking	3	die-cast zinc	black matte	60in (H) or greater NEMA 4 and NEMA 12	PDF
MHKD3	\$232.00	padlocking with defeater					PDF
MHKL3	\$251.00	combination keylocking/ padlocking					PDF
MHK1SS	\$234.00	padlocking	1	316 stainless steel	#4 brush	single-door NEMA 4X	PDF
MHKD1SS	\$258.00	padlocking with defeater					PDF
MHKL1SS	\$258.00	combination keylocking/ padlocking					PDF
MHK2SS	\$249.00	padlocking	3	316 stainless steel	#4 brush	less than 60in (H) NEMA 4X	PDF
MHKD2SS	\$274.00	padlocking with defeater					PDF
MHKL2SS	\$274.00	combination keylocking/ padlocking					PDF
MHK3SS	\$362.00	padlocking	3	316 stainless steel	#4 brush	60in (H) or greater NEMA 4X	PDF
MHKD3SS	\$398.00	padlocking with defeater					PDF
MHKL3SS	\$398.00	combination keylocking/ padlocking					PDF

Enclosure Accessories

Pull Handles



Features

- Black powder-coated carbon steel
- Package of 2
- Hardware included



[1427B2BK](#)

Pull Handles				
Part Number	Price	Handle Length	For Use With These Hammond Enclosures	Drawing Link
<u>1427B2BK</u>	\$6.00	1.25 [32]	Hammond RM1UxxxxxBK enclosures	<u>PDF</u>
<u>1427E1BK</u>	\$6.00	2.00 [51]	Hammond RM2UxxxxxBK enclosures	<u>PDF</u>
<u>1427P1BK</u>	\$9.75	2.80 [71]	Hammond RM3UxxxxxBK and RM4UxxxxxBK enclosures	<u>PDF</u>
Note: Dimensions in inches [millimeters].				

Enclosure Accessories

Locks and Latches

Eclipse Series 1-Point 1/4-Turn Handles



T-Handle



L-Handle

Features

- Field installable.
- Interchangeable with standard 1/4-turn latches on all Eclipse series enclosures.
- Keylocking latch assemblies include two keys.
- Maintain NEMA, UL and CSA ratings of enclosure.

Eclipse Series 1-Point 1/4-Turn Handles						
Part Number	Price	Style	Security	Material	Finish	Drawing Link
EHTL	\$68.00	1/4-turn tee handle	keylocking	die-cast zinc	black matte	PDF
EHLL	\$69.00	1/4-turn L-handle	keylocking	die-cast zinc	black matte	PDF
EHLNL	\$69.00	1/4-turn L-handle	—	die-cast zinc	black matte	PDF
EHLPL	\$127.00	1/4-turn L-handle	padlocking	zinc plated steel	—	PDF
EHLSS	\$310.00	1/4-turn L-handle	keylocking	316 stainless steel	—	PDF
EHLNLSS	\$310.00	1/4-turn L-handle	—	316 stainless steel	—	PDF
EHLPLSS	\$310.00	1/4-turn L-handle	padlocking	316 stainless steel	—	PDF