

# Rack Isolation Kit



## Application


The Rack Isolation Kit isolates open frame racks from conductive flooring to prevent multiple ground paths.

## Features

- Universal design works with most rack manufacturers.
- Use with Hammond and Rack Basics part numbers:
  - RB-2P
  - RB-2PA
  - DNRRHDW
  - DNRRHDKB
  - DC4R
- Open-ended design allows for retrofit installation.
- Isolation plates constructed of glass-reinforced thermoset polyester.
- Included in kit:
  - Two isolation plates
  - Four isolation grommets
- Bolt-down C4K-Z4 kit sold separately.
- Not compatible with DRZ4

## Listings

- TAA Compliant for GSA Schedule purchases



| Rack Isolation Kit                        |         |                          |                     |
|-------------------------------------------|---------|--------------------------|---------------------|
| Part Number                               | Price   | Overall Size WxD         | Drawing Link        |
| <a href="#">RIK19</a>                     | \$59.00 | 20.00 x 7.50 [508 x 191] | <a href="#">PDF</a> |
| <a href="#">RIK23</a>                     | \$64.00 | 24.00 x 7.50 [610 x 191] | <a href="#">PDF</a> |
| Note: Dimensions in inches [millimeters]. |         |                          |                     |

# Bonding Wire Kits

## Listings

- TAA Compliant for GSA Schedule purchases

## Features

- 12 in, 16 in [152 mm], or 22 in [559 mm] long, 10-gauge copper wire.
- Terminated with crimped-on terminals.
- Terminal hole is 0.256in [6.5mm] diameter.
- Includes mounting hardware for 1/4-20 or 10-32 ground studs.
- Includes stick-on grounding symbols (two for each jumper).



| Bonding Wire Kits        |         |                                                                                                                                                                 |                     |
|--------------------------|---------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|
| Part Number              | Price   | Description                                                                                                                                                     | Drawing Link        |
| <a href="#">GRDKIT01</a> | \$32.50 | Grounding strap, 12in length, 10 AWG Package of 2 Mounting hardware included                                                                                    | <a href="#">PDF</a> |
| <a href="#">GRDKIT02</a> | \$50.00 | Grounding strap, 16in length, 10 AWG, (2) #10-1/4in ring terminals Package of 6 #10-32 and 1/4-20 screws, washers and nuts included                             | <a href="#">PDF</a> |
| <a href="#">GRDKIT03</a> | \$9.25  | Grounding strap, 12in length, 10 AWG, (2) #10-1/4in ring terminals Package of 1 #10-32 screws, washers and nuts included                                        | <a href="#">PDF</a> |
| <a href="#">GRDKIT04</a> | \$50.00 | Grounding strap, 12in length, 10 AWG, (2) #10-1/4in ring terminals Package of 4 Quick-disconnect terminals, #10-32 and 1/4-20 screws, washers and nuts included | <a href="#">PDF</a> |
| <a href="#">GRDKIT05</a> | \$28.50 | Grounding strap, 22in length, 10 AWG, (2) #10-1/4in ring terminals Package of 1 Quick-disconnect terminals, #10-32 and 1/4-20 screws, washers and nuts included | <a href="#">PDF</a> |