


Waterfall Series IP69K Sanitary Wall-Mount



Features

- Designed to house electrical or electronic equipment and protect against harsh, industrial environments for wall-mount applications.
- Sloped top prevents water from resting on top as well as providing potential for controls mounting.
- Unique hinge design allows for easy cleaning in hose-down environments.

Construction

- Formed 304 or 316L stainless steel.
- Continuously welded seams ground smooth.
- Door stiffeners are provided where required for increased strength and rigidity – designed to also permit additional mounting options.
- Formed lip on enclosure to exclude flowing liquids and contaminants.
- Door latches (316 stainless steel quarter turns) feature the added safety of quarter turn slot requiring use of tool for opening.
- Door hinges (316 stainless steel) are easy to clean, provide 180° opening, are easily removed for modifications and are interchangeable.
- Uses waterfall series latches.
- Seamless poured-in-place gasket.
- Collar studs provided for mounting subpanel.
- Includes hardware kit with panel mounting nuts and sealing washers for wall-mounting holes.
- Bonding stud provided on door and grounding stud installed in enclosure.
- Cover and enclosure are natural stainless

steel with a smooth brushed finish.

Listings

- UL 508A Type 3R, 4, 4X, and 12 [File E65324]
- CSA Type 3R, 4, 4X, and 12 [File LR21001]
- NSF-ANSI 169 (not all accessories maintain NSF standards)
- Complies with:
 - NEMA Type 3R, 4, 4X, 12, and 13
 - IEC 60529, IP66, IP69K



Waterfall Series IP69K Sanitary Wall-Mount



Waterfall Series IP69K Sanitary Wall-Mount							
304 Stainless Steel	Price	316 Stainless Steel	Price	Enclosure Size HxWxD	Optional Subpanel	Price	Drawing Link
HWST16128SS	\$898.00	HWST16128S16	\$1,035.00	19.73 x 12.00 x 9.21 [501 x 305 x 234]	18P1309	\$32.50	PDF
HWST16168SS	\$989.00	HWST16168S16	\$1,139.00	19.73 x 16.00 x 9.21 [501 x 406 x 234]	18P1313	\$40.00	PDF
HWST201612SS	\$1,226.00	HWST201612S16	\$1,412.00	25.59 x 16.00 x 13.21 [650 x 406 x 336]	18P1713	\$48.00	PDF
HWST20168SS	\$1,094.00	HWST20168S16	\$1,260.00	23.73 x 16.00 x 9.21 [603 x 406 x 234]	18P1717	\$58.00	PDF
HWST202012SS	\$1,432.00	HWST202012S16	\$1,652.00	25.59 x 20.00 x 13.21 [650 x 508 x 336]	18P1713	\$48.00	PDF
HWST20208SS	\$1,249.00	HWST20208S16	\$1,437.00	23.73 x 20.00 x 9.21 [603 x 508 x 234]	18P1717	\$58.00	PDF
HWST24208SS	\$1,325.00	HWST24208S16	\$1,529.00	27.73 x 20.00 x 9.21 [704 x 508 x 234]	18P2121	\$86.00	PDF
HWST242412SS	\$1,653.00	HWST242412S16	\$1,909.00	29.59 x 24.00 x 13.21 [752 x 610 x 336]	18P2727	\$148.00	PDF
HWST24248SS	\$1,454.00	HWST24248S16	\$1,678.00	27.73 x 24.00 x 9.21 [704 x 610 x 234]	18P2721	\$105.00	PDF
HWST302412SS	\$1,875.00	HWST302412S16	\$2,165.00	35.59 x 24.00 x 13.21 [904 x 610 x 336]	18P2721	\$105.00	PDF
HWST30248SS	\$1,503.00	HWST30248S16	\$1,733.00	33.73 x 24.00 x 9.21 [857 x 610 x 234]	18P2727	\$148.00	PDF
HWST30308SS	\$1,883.00	HWST30308S16	\$2,175.00	33.73 x 30.00 x 9.21 [857 x 762 x 234]	18P2721	\$105.00	PDF
HWST363012SS	\$2,388.00	HWST363012S16	\$2,758.00	41.59 x 30.00 x 13.21 [1056 x 762 x 336]	18P3327	\$168.00	PDF
HWST363016SS	\$2,659.00	HWST363016S16	\$3,071.00	43.46 x 30.00 x 17.21 [1104 x 762 x 437]	18P3327	\$168.00	PDF
HWST36308SS	\$2,120.00	HWST36308S16	\$2,449.00	39.73 x 30.00 x 9.21 [1009 x 762 x 234]	18P3333	\$197.00	PDF
HWST363612SS	\$2,684.00	HWST363612S16	\$3,100.00	41.59 x 36.00 x 13.21 [1056 x 914 x 336]	18P3327	\$168.00	PDF
HWST483612SS	\$3,253.00	—	—	53.59 x 36.00 x 13.21 [1361 x 914 x 336]	18P4533	\$253.00	PDF
HWST483616SS	\$3,614.00	HWST483616S16	\$4,176.00	55.46 x 36.00 x 17.21 [1409 x 914 x 437]	18P4533	\$253.00	PDF
HWST603612SS	\$4,008.00	—	—	65.59 x 36.00 x 13.21 [1666 x 914 x 336]	18P5733	\$312.00	PDF
HWST603616SS	\$4,449.00	HWST603616S16	\$5,145.00	67.46 x 36.00 x 17.21 [1713 x 914 x 437]	18P5733	\$312.00	PDF

Note: Dimensions in inches [millimeters].

Enclosure Accessories

Locks and Latches



Waterfall Accessory Latch and Key			
Part Number	Price	Description	Drawing Link
EFGK	\$16.75	Hollow female round, 316L stainless steel. Package of 1. For use with EQTFG latches.	PDF
EQTFG	\$68.00	Replacement, easy-to-clean round, 1/4-turn sanitary, 1-point, 316L stainless steel. Package of 1. For use with Waterfall series enclosures. Requires EFGK key.	PDF
Note: Dimensions in inches [millimeters].			