

Enclosure Subpanels


1418, 1422, 1447, C3RxxxxHCR, HWxxxHK,
and HN4WM Wall-Mount Enclosures



Construction

- Steel panels are 12-gauge steel and are finished in RAL9003 white powder coat.
- Galvanized panels are 12-gauge unpainted galvanized steel.
- Stainless steel panels are 12-gauge and are brushed #4 316 SS.
- Aluminum panels are 5052-H32 aluminum alloy.
- Larger panels have two or four formed flanges.
- Some larger panels are 10-gauge.
- Panel mounting hardware not included (provided with enclosure).

Dimensions



Enclosure Subpanels

1418, 1422, 1447, C3RxxxxHCR, HWxxxHK,
and HN4WM Wall-Mount Enclosures



Subpanels - 1418, 1422, 1447, C3RxxxxHCR, HWxxxHK, and HN4WM Wall-Mount Enclosures										
Painted	Price	Galv.	Price	Aluminum	Price	Stainless	Price	Dimensions HxW	For Use With	Drawing Link
18P1309	\$32.50	18G1309	\$32.50	18A1309	\$47.50	18P1309S16	\$94.00	13.00 x 9.00 [330 x 229]	16x12 (HxW) 1418xxxx and C3R16126HCR	PDF
18P1313	\$40.00	18G1313	\$40.00	18A1313	\$59.00	18P1313S16	\$116.00	13.00 x 13.00 [330 x 330]	16x16 (HxW) 1418xxxx and C3R16166HCR	PDF
18P1515	\$44.00	18G1515	\$44.00	—	—	—	—	15.00 x 15.00 [381 x 381]	18x18 (HxW) C3R1818xxHCR	PDF
18P1709	\$38.00	18G1709	\$38.00	—	—	—	—	17.00 x 9.00 [432 x 229]	20x12 (HxW) 1418CA6 & 1418CA8	PDF
18P1713	\$48.00	18G1713	\$48.00	—	—	18P1713S16	\$138.00	17.00 x 13.00 [432 x 330]	20x16 (HxW) 1418xxxx and C3R20166HCR	PDF
18P1717	\$58.00	18G1717	\$58.00	18A1717	\$86.00	18P1717S16	\$177.00	17.00 x 17.00 [432 x 432]	20x20 (HxW) 1418xxxx, 1447SAxxHK and C3R20208HCR	PDF
18P2109	\$48.00	18G2109	\$48.00	—	—	—	—	21.00 x 9.00 [533 x 229]	24x12 (HxW) 1418xxxx	PDF
18P2113	\$55.00	18G2113	\$55.00	—	—	18P2113S16	\$171.00	21.00 x 13.00 [533 x 330]	24x16 (HxW) 1418xxxx and HW24168xxHK	PDF
18P2117	\$75.00	18G2117	\$75.00	18A2117	\$144.00	18P2117S16	\$215.00	21.00 x 17.00 [533 x 432]	24x20 (HxW) 1418xxxx, 1447SBxxHK, C3R24208HCR and HW2420xxxxHK	PDF
18P2121	\$86.00	18G2121	\$86.00	18A2121	\$167.00	18P2121S16	\$250.00	21.00 x 21.00 [533 x 533]	24x24 (HxW) 1418xxxx, 1447SCxxHK, C3R2424xxHCR and HW2424xxxxHK	PDF
18P2709	\$69.00	18G2709	\$69.00	—	—	—	—	27.00 x 9.00 [686 x 229]	30x12 (HxW) 1418KA8	PDF
18P2713	\$74.00	18G2713	\$74.00	—	—	—	—	27.00 x 13.00 [686 x 330]	30x16 (HxW) 1418FG6 & 1418KG8	PDF
18P2717	\$91.00	18G2717	\$91.00	—	—	18P2717S16	\$265.00	27.00 x 17.00 [686 x 432]	30x20 (HxW) 1418xxxx, 1447SDxxHK and HW30208xxHK	PDF
18P2721	\$105.00	18G2721	\$105.00	18A2721	\$199.00	18P2721S16	\$302.00	27.00 x 21.00 [686 x 533]	24x30/30x24 (HxW) 1418xxxx, 1447Sxxxx, C3R3024xxHCR and HWxxxxxxHK	PDF
18P2727	\$148.00	18G2727	\$148.00	—	—	18P2727S16	\$396.00	27.00 x 27.00 [686 x 686]	30x30 (HxW) 1418xxxx, C3R3030xxHCR and HW30308xxHK	PDF
18P3321	\$126.00	18G3321	\$126.00	18A3321	\$234.00	18P3321S16	\$381.00	33.00 x 21.00 [838 x 533]	36x24 (HxW) 1418xxxx, 1447Sxxxx, C3R362412HCR and HW3624xxxxHK	PDF
18P3327	\$168.00	18G3327	\$168.00	18A3327	\$287.00	18P3327S16	\$470.00	33.00 x 27.00 [838 x 686]	36x30 (HxW) 1418xxxx, 1447Sxxxx, C3R363012HCR and HW3630xxxxHK	PDF
18P3333	\$197.00	18G3333	\$197.00	—	—	18P3333S16	\$568.00	33.00 x 33.00 [838 x 838]	36x36 (HxW) 1418xxxx, C3R3636xxHCR and HW363612xxHK	PDF
18P3921	\$152.00	18G3921	\$152.00	—	—	—	—	39.00 x 21.00 [991 x 533]	24x42/42x24 (HxW) 1418N8, 1422Pxx and HN4WM24428xx	PDF
18P3927	\$192.00	18G3927	\$192.00	—	—	18P3927S16	\$554.00	39.00 x 27.00 [991 x 686]	30x42/42x30 (HxW) 1418xxxx, 1422R10, 1447Sxxxx, C3R423012HCR, HW423010xxHK and HN4WM304210xx	PDF
18P3933	\$225.00	18G3933	\$225.00	—	—	18P3933S16	\$663.00	39.00 x 33.00 [991 x 838]	36x42/42x36 (HxW) 1418xxxx, 1422UV12, 1447Sxxxx, C3R423612HCR, HW423610xxHK and HN4WM364210xx	PDF
18P4521	\$174.00	18G4521	\$174.00	—	—	—	—	45.00 x 21.00 [1143 x 533]	24x48/48x24 (HxW) 1418Q8, 1422PW8, 1447SQ10HK and HN4WM24488xx	PDF
18P4527	\$215.00	18G4527	\$215.00	—	—	—	—	45.00 x 27.00 [1143 x 686]	30x48/48x30 (HxW) 1418xxxx, 1422RW10 and HN4WM304810xx	PDF
18P4533	\$253.00	18G4533	\$253.00	18A4533	\$447.00	18P4533S16	\$717.00	45.00 x 33.00 [1143 x 838]	36x48/48x36 (HxW) 1418xxxx, 1422UW12, 1447Sxxxx, C3R4836xxHCR, HW4836xxxxHK and HN4WM364812xx	PDF
18P5733	\$312.00	18G5733	\$262.00	18A5733	\$554.00	18P5733S16	\$947.00	57.00 x 33.00 [1448 x 838]	36x60/60x36 (HxW) 1418xxxx, 1422UX12, 1447Sxxxx, C3R603612HCR, HW6036xxxxHK and HN4WM366012xx	PDF
18P6927	\$329.00	18G6927	\$329.00	—	—	—	—	69.00 x 27.00 [1753 x 686]	72x30 (HxW) 1418Uxx	PDF
18P6933	\$367.00	18G6933	\$367.00	—	—	—	—	69.00 x 33.00 [1753 x 838]	72x36 (HxW) 1418V12	PDF

Note: Dimensions in inches [millimeters].

Perforated Subpanels

1418, 1447, C3RxxxHCR and HWxxxHK
Wall-Mount Enclosures



Construction

- For use with 1418, 1447, C3RxxxHCR and HWxxxHK wall-mount enclosures.
- Made from 16-gauge steel.
- Accepts self-tapping screws eliminating timely measurement, marking and drilling of component mounting holes.
- 0.25in [6.35mm] diameter holes on 0.25in [6.4mm] staggered centers.
- ANSI 61 gray powder finish.

Subpanels for 1418, 1447, C3RxxxHCR and HWxxxHK Wall-Mount Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
18P1309PP	\$31.00	13.00 x 9.00 [330 x 229]	16x12 (HxW) 1418xxxx and C3R16126HCR	PDF
18P1313PP	\$38.00	13.00 x 13.00 [330 x 330]	16x16 (HxW) 1418xxxx and C3R16166HCR	PDF
18P1515PP	\$41.50	15.00 x 15.00 [381 x 381]	18x18 (HxW) C3R1818xxHCR	PDF
18P1713PP	\$45.00	17.00 x 13.00 [432 x 330]	20x16 (HxW) 1418xxxx and C3R20166HCR	PDF
18P1717PP	\$54.00	17.00 x 17.00 [432 x 432]	20x20 (HxW) 1418xxxx, 1447SAxxHK and C3R20208HCR	PDF
18P2117PP	\$71.00	21.00 x 17.00 [533 x 432]	24x20 (HxW) 1418xxxx, 1447SBxxHK, C3R24208HCR and HW2420xxxxHK	PDF
18P2121PP	\$81.00	21.00 x 21.00 [533 x 533]	24x24 (HxW) 1418xxxx, 1447SCxxHK, C3R2424xxHCR and HW2424xxxxHK	PDF
18P2721PP	\$98.00	27.00 x 21.00 [686 x 533]	24x30/30x24 (HxW) 1418xxxx, 1447Sxxxx, C3R3024xxHCR and HWxxxxxxHK	PDF
18P2727PP	\$139.00	27.00 x 27.00 [686 x 686]	30x30 (HxW) 1418xxxx, C3R3030xxHCR and HW30308xxHK	PDF
18P3321PP	\$119.00	33.00 x 21.00 [838 x 533]	36x24 (HxW) 1418xxxx, 1447Sxxxx, C3R362412HCR and HW3624xxxxHK	PDF
18P3327PP	\$157.00	33.00 x 27.00 [838 x 686]	36x30 (HxW) 1418xxxx, 1447Sxxxx, C3R363012HCR and HW3630xxxxHK	PDF
18P3333PP	\$185.00	33.00 x 33.00 [838 x 838]	36x36 (HxW) 1418xxxx, C3R3636xxHCR and HW363612xxHK	PDF

Note: Dimensions in inches [millimeters].

Dimensions

