

Enclosure Subpanels

N1A Enclosures



Construction


- 14-gauge steel finished in RAL9003 white powder coat.
- Subpanels and mounting hardware are included with N1A Series enclosures.



Subpanels for N1A Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
AP1612	\$16.25	13.00 x 10.50 [330 x 267]	16x12 (HxW) N1A1612x	PDF
AP1616	\$20.75	13.00 x 14.50 [330 x 368]	16x16 (HxW) N1A16167	PDF
AP1620	\$25.50	13.00 x 18.50 [330 x 470]	16x20 (HxW) N1A16207	PDF
AP2016	\$25.50	17.00 x 14.50 [432 x 368]	20x16 (HxW) N1A2016x	PDF
AP2416	\$31.00	21.00 x 14.50 [533 x 368]	24x16 (HxW) N1A24167	PDF
AP2020	\$34.50	17.00 x 18.50 [432 x 470]	20x20 (HxW) N1A2020x	PDF
AP2024	\$39.00	17.00 x 22.50 [432 x 572]	20x24 (HxW) N1A20249	PDF
AP2420	\$39.00	21.00 x 18.50 [533 x 470]	24x20 (HxW) N1A2420xx	PDF
AP2424	\$73.00	21.00 x 22.50 [533 x 572]	24x24 (HxW) N1A2424xx	PDF
AP3020	\$77.00	26.00 x 18.50 [660 x 470]	30x20 (HxW) N1A3020x	PDF
AP3024	\$98.00	26.00 x 22.50 [660 x 572]	30x24 (HxW) N1A3024xx	PDF
AP3030	\$98.00	26.00 x 28.50 [660 x 724]	30x30 (HxW) N1A30309	PDF
AP3624	\$100.00	32.00 x 22.50 [813 x 572]	36x24 (HxW) N1A3624x	PDF
AP4224	\$128.00	38.00 x 22.50 [965 x 572]	42x24 (HxW) N1A42249	PDF
AP4230	\$138.00	38.00 x 28.50 [965 x 724]	42x30 (HxW) N1A423012	PDF
AP3630	\$146.00	32.00 x 28.50 [813 x 724]	36x30 (HxW) N1A3630xx	PDF
AP4236	\$155.00	38.00 x 34.50 [965 x 876]	42x36 (HxW) N1A423612	PDF
AP4836	\$174.00	44.00 x 34.50 [1118 x 876]	48x36 (HxW) N1A483612	PDF


Note: Dimensions in inches [millimeters].

Dimensions



Perforated Subpanels

N1A Enclosures



Construction

- Made from 16-gauge steel.
- Accepts self-tapping screws eliminating timely measurement, marking and drilling of component mounting holes.
- 0.125in [3.175mm] diameter holes on 0.25in [6.4mm] staggered centers.
- ANSI 61 gray powder finish.

Perforated Subpanels for N1A Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
AP1612PP	\$17.50	13.00 x 10.50 [330 x 267]	16x12 (HxW) N1A1612x	PDF
AP1616PP	\$22.50	13.00 x 14.50 [330 x 368]	16x16 (HxW) N1A1616x	PDF
AP1620PP	\$27.50	13.00 x 18.50 [330 x 470]	16x20 (HxW) N1A1620x	PDF
AP2016PP	\$27.50	17.00 x 14.50 [432 x 368]	20x16 (HxW) N1A2016x	PDF
AP2020PP	\$37.50	17.00 x 18.50 [432 x 470]	20x20 (HxW) N1A2020x	PDF
AP2024PP	\$42.50	17.00 x 22.50 [432 x 572]	20x24 (HxW) N1A2024x	PDF
AP2416PP	\$34.00	21.00 x 14.50 [533 x 368]	24x16 (HxW) N1A2416x	PDF
AP2420PP	\$42.50	21.00 x 18.50 [533 x 470]	24x20 (HxW) N1A2420xx	PDF
AP2424PP	\$80.00	21.00 x 22.50 [533 x 572]	24x24 (HxW) N1A2424xx	PDF
AP3020PP	\$93.00	26.00 x 18.50 [660 x 470]	30x20 (HxW) N1A3020x	PDF
AP3024PP	\$106.00	26.00 x 22.50 [660 x 572]	30x24 (HxW) N1A3024xx	PDF
AP3030PP	\$129.00	26.00 x 28.50 [660 x 724]	30x30 (HxW) N1A3030x	PDF
AP3624PP	\$109.00	32.00 x 22.50 [813 x 572]	36x24 (HxW) N1A3624x	PDF
AP3630PP	\$157.00	32.00 x 28.50 [813 x 724]	36x30 (HxW) N1A3630xx	PDF
AP4224PP	\$184.00	38.00 x 22.50 [965 x 572]	42x24 (HxW) N1A4224x	PDF

Note: Dimensions in inches [millimeters].

Dimensions

