

# Enclosure Subpanels


## N1J and C3RxxxHCR Enclosures



### Construction

- Replacement panels for N1J enclosures.
- Optional panels for C3RxxxHCR enclosures.
- Made from 16-gauge steel.
- RAL9003 white powder finish.

### Dimensions




Subpanels for N1J and C3RxxxHCR Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
<a href="#">N1JP64</a>	\$5.25	4.25 x 2.25 [108 x 57]	6x4 (HxW) C3R644HCR	<a href="#">PDF</a>
<a href="#">N1JP66</a>	\$5.25	4.25 x 4.25 [108 x 108]	6x6 (HxW) N1J664 and C3R664HCR	<a href="#">PDF</a>
<a href="#">N1JP86</a>	\$6.25	6.25 x 4.25 [159 x 108]	8x6 (HxW) N1J864 and C3R864HCR	<a href="#">PDF</a>
<a href="#">N1JP88</a>	\$7.25	6.25 x 6.25 [159 x 159]	8x8 (HxW) N1J88x and C3R886HCR	<a href="#">PDF</a>
<a href="#">N1JP108</a>	\$8.50	8.25 x 6.25 [210 x 159]	10x8 (HxW) N1J108x and C3R1086HCR	<a href="#">PDF</a>
<a href="#">N1JP1010</a>	\$9.75	8.25 x 8.25 [210 x 210]	10x10 (HxW) N1J1010x	<a href="#">PDF</a>
<a href="#">N1JP1210</a>	\$11.50	10.25 x 8.25 [260 x 210]	12x10 (HxW) N1J1210x and C3R12106HCR	<a href="#">PDF</a>
<a href="#">N1JP1212</a>	\$13.50	10.25 x 10.25 [260 x 260]	12x12 (HxW) N1J1212x and C3R1212xxHCR	<a href="#">PDF</a>
<a href="#">N1JP1412</a>	\$15.00	12.25 x 10.25 [311 x 260]	14x12 (HxW) N1J1412x	<a href="#">PDF</a>
<a href="#">N1JP1612</a>	\$17.00	14.25 x 10.25 [362 x 260]	16x12 (HxW) N1J16126	<a href="#">PDF</a>
<a href="#">N1JP2012</a>	\$20.75	18.25 x 10.25 [464 x 260]	20x12 (HxW) N1J20126	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# Perforated Subpanels

## N1J and C3RxxxHCR Enclosures



### Construction

- Made from 16-gauge steel.
- Accepts self-tapping screws eliminating timely measurement, marking and drilling of component mounting holes.
- 0.25in [6.35mm] diameter holes on 0.25in [6.4mm] staggered centers.
- ANSI 61 gray powder finish.

Perforated Subpanels for N1J and C3RxxxHCR Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
<a href="#">N1JP66PP</a>	\$5.75	4.25 x 4.25 [108 x 108]	6x6 (HxW) N1J664 and C3R664HCR	<a href="#">PDF</a>
<a href="#">N1JP86PP</a>	\$6.75	6.25 x 4.25 [159 x 108]	8x6 (HxW) N1J864 and C3R864HCR	<a href="#">PDF</a>
<a href="#">N1JP88PP</a>	\$7.75	6.25 x 6.25 [159 x 159]	8x8 (HxW) N1J88x and C3R886HCR	<a href="#">PDF</a>
<a href="#">N1JP108PP</a>	\$9.25	8.25 x 6.25 [210 x 159]	10x8 (HxW) N1J108x and C3R1086HCR	<a href="#">PDF</a>
<a href="#">N1JP1010PP</a>	\$10.50	8.25 x 8.25 [210 x 210]	10x10 (HxW) N1J1010x	<a href="#">PDF</a>
<a href="#">N1JP1210PP</a>	\$12.25	10.25 x 8.25 [260 x 210]	12x10 (HxW) N1J1210x and C3R12106HCR	<a href="#">PDF</a>
<a href="#">N1JP1212PP</a>	\$14.75	10.25 x 10.25 [260 x 260]	12x12 (HxW) N1J1212x and C3R1212xxHCR	<a href="#">PDF</a>
<a href="#">N1JP1412PP</a>	\$16.25	12.25 x 10.25 [311 x 260]	14x12 (HxW) N1J1412x	<a href="#">PDF</a>
<a href="#">N1JP1612PP</a>	\$18.50	14.25 x 10.25 [362 x 260]	16x12 (HxW) N1J16126	<a href="#">PDF</a>
<a href="#">N1JP2012PP</a>	\$22.50	18.25 x 10.25 [464 x 260]	20x12 (HxW) N1J20126	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

### Dimensions

