UR20-8DO-N Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Weidmuller UR20 series discrete output module, 8-point, 24 VDC, sinking, 1 common(s), 8 point(s) per common, 0.5A/point, 4A/module. Removable terminal blocks included.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/UR20-8DO-N

Technical Specifications

Brand	Weidmuller
Item	Output module
I/O Module Type	Discrete
Series	UR20
Number of Output Points	8
Nominal Output Voltage	24 VDC
Discrete Output Type	Sinking
Number of Non-Isolated Output Commons	1
Number of Points per Common	8
Load Current	0.5A/point, 4A/module
Includes	Removable terminal blocks
Programming Software	None, configure via Internet browser

Agency Approvals

UL Listed File #	E141197
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/UR20-8DO-N.pdf
See store item page for other formats.