# Mini Cordsets and Receptacles Accessories

## Mini "T" Connectors Features and General Specifications

- Oil-resistant yellow PVC body
- Copper alloy/gold plating contacts
- Nickel-plated brass coupling nut
- Operating temperature range: -40 to 105°C [-40 to 221°F]
- IP67 protection when connected
- Approvals: UL File E328610, CE
- Made in the USA

### Mini "T" Connectors

| Face View of Male | Face View of Female | # of Poles | Rating | Part Number | Wiring | Price |
|---|---|---|---|---|---|---|
|  |  | 3 | 300V 8A | ZP-S1-3MFF-T | 1 – 1 – 1<br>2 – 2 – 2<br>3 – 3 – 3 | $46.00 |
|  |  | 4 | 300V 8A | ZP-S1-4MFF-T | 1 – 1 – 1<br>2 – 2 – 2<br>3 – 3 – 3<br>4 – 4 – 4 | $48.00 |
|  |  | 5 | 300V 8A | ZP-S1-5MFF-T | 1 – 1 – 1<br>2 – 2 – 2<br>3 – 3 – 3<br>4 – 4 – 4<br>5 – 5 – 5 | $67.00 |

### Caps and Adapters

| Dimensions – mm [in] | Description | Part Number | Price |
|---|---|---|---|
|  | Closure cap for covering receptacles and plugs with male threads. 0.17" diameter mounting hole for securing the chain. Clear anodized aluminum with nickel-plated brass chain and hardware. | ZP-S1-CAP | $5.75 |
|  | Closure plug for covering receptacles and plugs with female threads. 017" diameter mounting hole for securing the chain. Clear anodized aluminum with nickel-plated brass chain and hardware. | ZP-S1-PLUG | $8.00 |
| | Adapter coupling for connecting male and female plugs with female couplings. Clear anodized aluminum. | ZP-S1-XMP-AD | $4.00 |

## Dimensions

mm [in]




Note: Tightening torque 44 lb·in (5.0 N·m) coupling nut.