

# KILLARK XCS Series Control Station Cover Assemblies - Pilot Lights

## Listings

- Listed; File E53360
- Class I, Div. 1 & 2, Groups C, D
- Class II, Div. 1 & 2, Groups E, F, G
- Class III
- NEMA 7 (C, D) 9 (E, F, G)
- CSA Certified; File LR11714
- Class I, Zones 1 & 2, Groups IIB, IIA



Pilot Light



Double Pilot Light

Pilot Light /  
PushbuttonPilot Light /  
Two Mini Pushbutton

| XCS Pilot Light                 |          |                     |                    |         |             |            |                      |
|---------------------------------|----------|---------------------|--------------------|---------|-------------|------------|----------------------|
| Part Number<br>(cover included) | Price    | Drawing<br>Link     | Description        | Diagram | LED Voltage | Lens Color | Legend Plate Marking |
| <a href="#">XCS-0B24ALD</a>     | \$370.00 | <a href="#">PDF</a> | Single pilot light |         | 110 VAC/VDC | Amber      | Blank plate          |
| <a href="#">XCS-0B24CLD</a>     | \$296.00 | <a href="#">PDF</a> | Single pilot light |         | 110 VAC/VDC | Clear      | Blank plate          |
| <a href="#">XCS-0B24GLD</a>     | \$259.00 | <a href="#">PDF</a> | Single pilot light |         | 110 VAC/VDC | Green      | Blank plate          |
| <a href="#">XCS-0B24RLD</a>     | \$259.00 | <a href="#">PDF</a> | Single pilot light |         | 110 VAC/VDC | Red        | Blank plate          |

| XCS Double Pilot Light          |          |                     |                  |         |             |             |                      |
|---------------------------------|----------|---------------------|------------------|---------|-------------|-------------|----------------------|
| Part Number<br>(cover included) | Price    | Drawing<br>Link     | Description      | Diagram | LED Voltage | Lens Colors | Legend Plate Marking |
| <a href="#">XCS-0B30ALD</a>     | \$631.00 | <a href="#">PDF</a> | Two pilot lights |         | 110 VAC/VDC | Amber Amber | Two blank plates     |
| <a href="#">XCS-0B30CLD</a>     | \$380.00 | <a href="#">PDF</a> | Two pilot lights |         | 110 VAC/VDC | Clear Clear | Two blank plates     |
| <a href="#">XCS-0B30GLD</a>     | \$361.00 | <a href="#">PDF</a> | Two pilot lights |         | 110 VAC/VDC | Green Green | Two blank plates     |
| <a href="#">XCS-0B30RLD</a>     | \$538.00 | <a href="#">PDF</a> | Two pilot lights |         | 110 VAC/VDC | Red Red     | Two blank plates     |
| <a href="#">XCS-0B30RLD-GLD</a> | \$380.00 | <a href="#">PDF</a> | Two pilot lights |         | 110 VAC/VDC | Red Green   | Two blank plates     |

| XCS Momentary Contact Pushbutton and Pilot Light |          |                     |                                           |         |             |                     |            |                                              |
|--------------------------------------------------|----------|---------------------|-------------------------------------------|---------|-------------|---------------------|------------|----------------------------------------------|
| Part Number<br>(cover included)                  | Price    | Drawing<br>Link     | Description                               | Diagram | LED Voltage | Pushbutton<br>Color | Lens Color | Legend Plate Marking                         |
| <a href="#">XCS-0B13-CD</a>                      | \$267.00 | <a href="#">PDF</a> | 1 N.C. momentary operator and pilot light |         | 110 VAC/VDC | Red                 | Clear      | Pushbutton: "STOP" Pilot light: Blank plate  |
| <a href="#">XCS-0B13-OD</a>                      | \$267.00 | <a href="#">PDF</a> | 1 N.O. momentary operator and pilot light |         | 110 VAC/VDC | Green               | Red        | Pushbutton: "START" Pilot light: Blank plate |
| <a href="#">XCS-0B13-UD</a>                      | \$337.00 | <a href="#">PDF</a> | 1 N.O. / 1 N.C. momentary and pilot light |         | 110 VAC/VDC | Black               | Red        | Two blank plates                             |

| XCS Two Mini Momentary Contact Pushbuttons and Pilot Light |          |                     |                                                                                                                        |         |             |                      |            |                                                                           |
|------------------------------------------------------------|----------|---------------------|------------------------------------------------------------------------------------------------------------------------|---------|-------------|----------------------|------------|---------------------------------------------------------------------------|
| Part Number<br>(cover included)                            | Price    | Drawing<br>Link     | Description                                                                                                            | Diagram | LED Voltage | Pushbutton<br>Colors | Lens Color | Legend Plate Marking                                                      |
| <a href="#">XCS-0A15D</a>                                  | \$424.00 | <a href="#">PDF</a> | Mini red operator with 1 N.C. momentary contact and mini green operator with 1 N.O. momentary contact, and pilot light |         | 110 VAC/VDC | Green Red            | Red        | N.O. Pushbutton: "START" N.C. Pushbutton: "STOP" Pilot light: Blank plate |

\* We also offer a large selection of optional legend plates. See accessories later in this section.

# KILLARK SWB Series Splice/Device Boxes For Use With XCS Cover Assemblies

**SWB-2****SWB-5****SWB-8****SWB-11****SWB-42**

## Listings

- UL Listed; File E53360
- Class I, Div. 1 & 2, Groups C, D
- Class II, Div. 1 & 2, Groups E, F, G
- Class III
- NEMA 7 (C, D) 9 (E, F, G)
- CSA Certified; File LR11712
- Class I, Zones 1 & 2, Groups IIB, IIA



### SWB Device Bodies

| <i>Part Number</i>   | <i>Price</i> | <i>Drawing Link</i> | <i>Description</i>                      | <i>Hub Size (inches)</i> |
|----------------------|--------------|---------------------|-----------------------------------------|--------------------------|
| <b><u>SWB-2</u></b>  | \$66.00      | <a href="#">PDF</a> | Single gang / Dead-end                  | 3/4                      |
| <b><u>SWB-5</u></b>  | \$67.00      | <a href="#">PDF</a> | Single gang / Feed-through              | 3/4                      |
| <b><u>SWB-8</u></b>  | \$129.00     | <a href="#">PDF</a> | Double gang / Dead-end                  | 3/4                      |
| <b><u>SWB-11</u></b> | \$128.00     | <a href="#">PDF</a> | Double gang / Feed-through              | 3/4                      |
| <b><u>SWB-42</u></b> | \$187.00     | <a href="#">PDF</a> | Single gang / Dead-end / Deep style     | 3/4                      |
| <b><u>SWB-45</u></b> | \$230.00     | <a href="#">PDF</a> | Single gang / Feed-through / Deep style | 3/4                      |