KILLARK FXCS Series Factory Sealed Control Station Cover Assemblies and Selector Switches

Selector Switch

Key-Operated Selector Switch

Listings

- UL Listed; File E53360
- Class I, Div. 1 & 2, Groups C, D
- Class II, Div. 1 & 2, Groups E, F, G
- Class III
- NEMA 3, 7 (C, D) 9 (E, F, G)
- CSA Certified; File LR11714
- Class I, Zones 1 & 2, Groups IIB, IIA

FXCS Two-Position Maintained Contact Selector Switches

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Right Position Left Contact	Right Position Right Contact	Knob Color	Legend Plate Marking*
FXCS-0S2A1	$418.00	PDF	1 N.O. / 1 N.C.					Black	"OFF ON""
FXCS-0S2A5	$393.00	PDF	2 N.O. / 2 N.C.					Black	"OFF ON""

FXCS Two-Position Key-Operated Maintained Contact Selector Switches

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Right Position Left Contact	Right Position Right Contact	Key Removal	Legend Plate Marking*
FXCS-0K2A1A	$631.00	PDF	1 N.O. / 1 N.C.					Any position	"OFF ON"
FXCS-0K2A5A	$667.00	PDF	2 N.O. / 2 N.C.					Any position	"OFF ON"

FXCS Three-Position Maintained Contact Selector Switches

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Center Position Left Contact	Center Position Right Contact	Right Position Left Contact	Right Position Right Contact	Knob Color	Legend Plate Marking*
FXCS-0S3C4	$421.00	PDF	1 N.O. / 1 N.C.							Black	"HAND OFF AUTO"
FXCS-0S3C5	$402.00	PDF	2 N.O. / 2 N.C.							Black	"HAND OFF AUTO"

FXCS Three-Position Key-Operated Maintained Contact Selector Switches

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Center Position Left Contact	Center Position Right Contact	Right Position Left Contact	Right Position Right Contact	Key Removal	Legend Plate Marking*
FXCS-0K3C4A	$535.00	PDF	1 N.O. / 1 N.C.							Any position	"HAND OFF AUTO"
FXCS-0K3C5A	$485.00	PDF	2 N.O. / 2 N.C.							Any position	"HAND OFF AUTO"

*** We also offer a large selection of optional legend plates. See accessories later in this section.**

KILLARK FXCS Series Factory Sealed Control Station Cover Assemblies and Selector Switches - Continued

Selector Switch

Key-Operated Selector Switch

FXCS Two-Position Spring Return Selector Switch

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Right Position Left Contact	Right Position Right Contact	Legend Plate Marking*
FXCS-0S2L3F	$496.00	PDF	1 N.O. / 1 N.C., spring return from right					"OFF" / "ON""

FXCS Two-Position Key-Operated Spring Return Selector Switches

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Right Position Left Contact	Right Position Right Contact	Key Removal	Legend Plate Marking*
FXCS-0K2L3F22A	$669.00	PDF	1 N.O. / 1 N.C., spring return from right					left position only	"OFF" / "ON""

FXCS Three-Position Spring Return Selector Switches

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Center Position Left Contact	Center Position Right Contact	Right Position Left Contact	Right Position Right Contact	Knob Color	Legend Plate Marking*
FXCS-0S3M6G	$411.00	PDF	2 N.O., spring return to center from left or right							Black	"HAND OFF AUTO"
FXCS-0S3L6G	$411.00	PDF	2 N.O., spring return to center from right, maintained in center and left							Black	"HAND OFF AUTO"
FXCS-0S3R6G	$411.00	PDF	2 N.O., spring return to center from left, maintained in center and right							Black	"HAND OFF AUTO"

FXCS Three-Position Key-Operated Spring Return Selector Switches

Part Number (cover included)	Price	Drawing Link	Description	Left Position Left Contact	Left Position Right Contact	Center Position Left Contact	Center Position Right Contact	Right Position Left Contact	Right Position Right Contact	Key Removal	Legend Plate Marking*
FXCS-0K3M6G32A	$613.00	PDF	2 N.O., spring return to center from left or right							center position only	"HAND OFF AUTO"
FXCS-0K3L6G32A	$613.00	PDF	2 N.O., spring return to center from right, maintained in center and left							center position only	"HAND OFF AUTO"
FXCS-0K3R6G32A	$581.00	PDF	2 N.O., spring return to center from left, maintained in center and right							center position only	"HAND OFF AUTO"

*** We also offer a large selection of optional legend plates. See accessories later in this section.**

KILLARK FXB Series Factory Sealed Splice/Device Boxes for FXCS Series Cover Assemblies

FXB-2
Dead End

FXB-5
Feed Through

FXB-8
Double Gang Dead End

FXB-11
Double Gang Feed Through

Features

Splice Boxes
The FXB series of splice boxes are designed for use with the FXCS series cover sub-assemblies.

Listings

- UL Listed; File E53360
- Class I, Div. 1 & 2, Groups C, D
- Class II, Div. 1 & 2, Groups E, F, G
- Class III
- NEMA 3, 7 (C, D) 9 (E, F, G)
- CSA Certified; File LR11714
- Class I, Zones 1 & 2, Groups IIB, IIA

FXB Splice/Device Box Selection and Dimensions

Part Number	Price	Drawing Link	Description	NPT Hub Size (inches)
FXB-1	$70.00	PDF	Single gang / Dead-end	1/2
FXB-2	$66.00	PDF	Single gang / Dead-end	3/4
FXB-3	$79.00	PDF	Single gang / Dead-end	1
FXB-4	$71.00	PDF	Single gang / Feed-through	1/2
FXB-5	$73.00	PDF	Single gang / Feed-through	3/4
FXB-6	$94.00	PDF	Single gang / Feed-through	1
FXB-7	$160.00	PDF	Double gang / Dead-end	1/2
FXB-8	$137.00	PDF	Double gang / Dead-end	3/4
FXB-9	$136.00	PDF	Double gang / Dead-end	1
FXB-10	$138.00	PDF	Double gang / Feed-through	1/2
FXB-11	$140.00	PDF	Double gang / Feed-through	3/4
FXB-12	$138.00	PDF	Double gang / Feed-through	1