



## SureStep® Linear Actuators Cables

Cables for SureStep Series Linear Actuators			
Part Number	Price	Description	Drawing
<a href="#">STP-LA-EXT17-006</a>	\$25.00	SureStep extension cable, 6-pin (4-wire) connector to pigtail, 6ft cable length. For use with SureStep NEMA 17 STP-LE series linear actuators.	<a href="#">PDF</a>
<a href="#">STP-LA-EXT17-010</a>	\$32.00	SureStep extension cable, 6-pin (4-wire) connector to pigtail, 10ft cable length. For use with SureStep NEMA 17 STP-LE series linear actuators.	<a href="#">PDF</a>
<a href="#">STP-LA-EXT17-020</a>	\$53.00	SureStep extension cable, 6-pin (4-wire) connector to pigtail, 20ft cable length. For use with SureStep NEMA 17 STP-LE series linear actuators.	<a href="#">PDF</a>
<a href="#">STP-LA-EXT23-006</a>	\$28.00	SureStep extension cable, 6-pin (4-wire) connector to pigtail, 6ft cable length. For use with SureStep NEMA 23 STP-LE series linear actuators.	<a href="#">PDF</a>
<a href="#">STP-LA-EXT23-010</a>	\$37.00	SureStep extension cable, 6-pin (4-wire) connector to pigtail, 10ft cable length. For use with SureStep NEMA 23 STP-LE series linear actuators.	<a href="#">PDF</a>
<a href="#">STP-LA-EXT23-020</a>	\$57.00	SureStep extension cable, 6-pin (4-wire) connector to pigtail, 20ft cable length. For use with SureStep NEMA 23 STP-LE series linear actuators.	<a href="#">PDF</a>

### STP-LA-EXT17-0xx Dimensions (mm [in])



VIEW FROM WIRE ENTRANCE



PINOUT CHART		
PIN #	COLOR	WIRE
1	RED	A+
2	N/A	
3	YELLOW	A-
4	GREEN	B+
5	N/A	
6	BLACK	B-

CABLES		
CABLE PART #	LENGTH L (IN)	LENGTH L (mm)
STP-LA-EXT17-006	72	1828
STP-LA-EXT17-010	120	3048
STP-LA-EXT17-020	240	6096



[STP-LA-EXT17-006](#)

### STP-LA-EXT23-0xx Dimensions (mm [in])



VIEW FROM WIRE ENTRANCE

PINOUT CHART		
PIN #	COLOR	WIRE
1	RED	A+
2	N/A	
3	WHITE	A-
4	GREEN	B+
5	N/A	
6	BLACK	B-

CABLES		
CABLE PART #	LENGTH L (IN)	LENGTH L (mm)
STP-LA-EXT23-006	72	1828
STP-LA-EXT23-010	120	3048
STP-LA-EXT23-020	240	6096



[STP-LA-EXT23-006](#)