



# LS Electric AC Servo Systems

## Accessories, *continued*

**NOTE:** These parts available for sale to North American locations only

### L7C/L7P/iX7NH System Motor Brake Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<a href="#"><u>APCS-BN03QS-AD</u></a>	\$52.00	N	3m [9.8 ft]	18AWG	<a href="#"><u>PDF</u></a>	APMC FBL/FCL brake motors (100W – 1kW)
<a href="#"><u>APCS-BN05QS-AD</u></a>	\$55.00		5m [16.4 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-BN10QS-AD</u></a>	\$61.00		10m [32.8 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-BN20QS-AD</u></a>	\$74.00		20m [65.6 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-BF03QS-AD</u></a>	\$58.00	Y	3m [9.8 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-BF05QS-AD</u></a>	\$63.00		5m [16.4 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-BF10QS-AD</u></a>	\$79.00		10m [32.8 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-BF20QS-AD</u></a>	\$108.00		20m [65.6 ft]		<a href="#"><u>PDF</u></a>	



**APCS-BN series brake cable**

# LS ELECTRIC L7C Series AC Servo Systems

## Accessories, *continued*

**NOTE:** These parts available for sale to North American locations only

### L7C System Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<a href="#"><u>APCS-PN03LSC-AD</u></a>	\$40.00	N	3m [9.8 ft]	18AWG	<a href="#"><u>PDF</u></a>	APMC FBL/FCL motors (100W – 1kW) used with L7C drives
<a href="#"><u>APCS-PN05LSC-AD</u></a>	\$48.00		5m [16.4 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-PN10LSC-AD</u></a>	\$62.00		10m [32.8 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-PN20LSC-AD</u></a>	\$85.00		20m [65.6 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-PF03LSC-AD</u></a>	\$52.00	Y	3m [9.8 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-PF05LSC-AD</u></a>	\$68.00		5m [16.4 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-PF10LSC-AD</u></a>	\$96.00		10m [32.8 ft]		<a href="#"><u>PDF</u></a>	
<a href="#"><u>APCS-PF20LSC-AD</u></a>	\$151.00		20m [65.6 ft]		<a href="#"><u>PDF</u></a>	



**APCS-PN series motor cable**

## L7P System Non-Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
<a href="#">APCS-PN03LS-AD</a>	\$42.00	N	3m [9.8 ft]	18AWG	<a href="#">PDF</a>	FBL/FCL series motors
<a href="#">APCS-PN05LS-AD</a>	\$46.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10LS-AD</a>	\$57.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20LS-AD</a>	\$80.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03LS-AD</a>	\$53.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05LS-AD</a>	\$62.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10LS-AD</a>	\$90.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20LS-AD</a>	\$145.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03HS-AD</a>	\$37.00	N	3m [9.8 ft]	14AWG	<a href="#">PDF</a>	APM-FE series motors without brake
<a href="#">APCS-PN05HS-AD</a>	\$44.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10HS-AD</a>	\$62.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20HS-AD</a>	\$98.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03HS-AD</a>	\$52.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05HS-AD</a>	\$66.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10HS-AD</a>	\$106.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20HS-AD</a>	\$184.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03IS-AD</a>	\$50.00	N	3m [9.8 ft]	14AWG	<a href="#">PDF</a>	230VAC APM-FF35D and 460VAC APM-FFP35D motors without brakes
<a href="#">APCS-PN05IS-AD</a>	\$64.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10IS-AD</a>	\$98.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20IS-AD</a>	\$167.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03IS-AD</a>	\$64.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05IS-AD</a>	\$85.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10IS-AD</a>	\$140.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20IS-AD</a>	\$252.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03JS-AD</a>	\$58.00	N	3m [9.8 ft]	10AWG	<a href="#">PDF</a>	230VAC APM-FF55D motors without brake
<a href="#">APCS-PN05JS-AD</a>	\$77.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10JS-AD</a>	\$120.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20JS-AD</a>	\$220.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03JS-AD</a>	\$83.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05JS-AD</a>	\$116.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10JS-AD</a>	\$203.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20JS-AD</a>	\$376.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03JS1-AD</a>	\$69.00	Y	3m [9.8 ft]	12AWG	<a href="#">PDF</a>	460VAC APM-FFP55D and APM-FFP75D motors without brakes
<a href="#">APCS-PF05JS1-AD</a>	\$95.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10JS1-AD</a>	\$159.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20JS1-AD</a>	\$289.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03JS2-AD</a>	\$99.00	N	3m [9.8 ft]	8AWG	<a href="#">PDF</a>	230VAC APM-FF75D motors without brake
<a href="#">APCS-PN05JS2-AD</a>	\$139.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10JS2-AD</a>	\$235.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20JS2-AD</a>	\$427.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03JS2-AD</a>	\$144.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05JS2-AD</a>	\$210.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10JS2-AD</a>	\$374.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20JS2-AD</a>	\$703.00		20m [65.6 ft]		<a href="#">PDF</a>	

NOTE: These parts available for sale to North American locations only



**APCS-PxxLS series power cable**



**APCS-PxxHS series power cable**



**APCS-PxxIS series power cable**



**APCS-PxxJS series power cable**

## Accessories, continued

### L7P System Brake Motor Power Cables

Part Number	Price	Flex Rated	Length	Gauge	Drawing	Compatible Motors
Note: For FBL/FCL 100W-1kW motors with brake, use the power cables on page tMNC-234 (APCS-PxxxLS-AD) AND separate brake cable APCS-BxxxQS-AD from page tMNC-232. This is for FBL/FCL motors only. FE and FF motors have brake wiring incorporated into the power cable (below).						
<a href="#">APCS-PN03NB-AD</a>	\$49.00	N	3m [9.8 ft]	14AWG	<a href="#">PDF</a>	230VAC and 460VAC APM-FE series motors with brakes
<a href="#">APCS-PN05NB-AD</a>	\$58.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10NB-AD</a>	\$84.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20NB-AD</a>	\$137.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03NB-AD</a>	\$71.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05NB-AD</a>	\$95.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10NB-AD</a>	\$153.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20NB-AD</a>	\$274.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03PB-AD</a>	\$69.00	N	3m [9.8 ft]		<a href="#">PDF</a>	230VAC APM-FF35D and 460VAC APM-FFP35D motors with brakes
<a href="#">APCS-PN05PB-AD</a>	\$87.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10PB-AD</a>	\$133.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20PB-AD</a>	\$229.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03PB-AD</a>	\$88.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05PB-AD</a>	\$120.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10PB-AD</a>	\$198.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20PB-AD</a>	\$359.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03LB-AD</a>	\$66.00	N	3m [9.8 ft]	8AWG	<a href="#">PDF</a>	230VAC APM-FF55D motors with brake
<a href="#">APCS-PN05LB-AD</a>	\$84.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10LB-AD</a>	\$131.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20LB-AD</a>	\$226.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03LB-AD</a>	\$96.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05LB-AD</a>	\$136.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10LB-AD</a>	\$235.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20LB-AD</a>	\$435.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03LB1-AD</a>	\$81.00	Y	3m [9.8 ft]	12AWG	<a href="#">PDF</a>	460VAC APM-FFP55D and APM-FFP75D motors with brakes
<a href="#">APCS-PF05LB1-AD</a>	\$110.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10LB1-AD</a>	\$187.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20LB1-AD</a>	\$341.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN03LB2-AD</a>	\$110.00	N	3m [9.8 ft]	8AWG	<a href="#">PDF</a>	230VAC APM-FF75D motors with brake
<a href="#">APCS-PN05LB2-AD</a>	\$151.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN10LB2-AD</a>	\$255.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PN20LB2-AD</a>	\$460.00		20m [65.6 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF03LB2-AD</a>	\$159.00	Y	3m [9.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF05LB2-AD</a>	\$232.00		5m [16.4 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF10LB2-AD</a>	\$410.00		10m [32.8 ft]		<a href="#">PDF</a>	
<a href="#">APCS-PF20LB2-AD</a>	\$772.00		20m [65.6 ft]		<a href="#">PDF</a>	



**APCS-PxxNB series power cable**



**APCS-PxxPB series power cable**



**APCS-PxxLB series power cable**